



SKU # RS-CREE-10BARHD

Part # 1004301

Description

10in Heavy Duty Series CREE Combo LED Light Bar Race Sport Lighting



Categories Truck, Powersports, Agricultural, Jeep, LED Light Bars

Sub-Categories

LED Light Bars, Heavy Duty PROFESSIONAL Series Dual Row LED Light Bars - Lifetime Warranty, Heavy Duty PROFESSIONAL Series Dual Row LED Light Bars - Lifetime Warranty, Heavy Duty Series Dual Row LED Light Bars, Heavy Duty Series Dual Row Light Bars

UPC 811712024181

Unit of Measure EA

Related Skus:

Cross Sell Skus:

Condition

New

Manufacturer

Race Sport Lighting

EZ Category

HD Series Dual Row Light Bars

Harmonization Code

8512.20.2080

Universal

YES

Life Expectancy

50,000 hours

SEMA Product Light Bar

Part Type ID 1069

Reverse Polarity

Light Bar

Operating Voltage

12-32VDC

Current Draw

5.7A

Wattage

60-Watts

Chip Type

CREE

IP Rating

IP68

LUX

Product Information

Premium light bars for serious off-roading and demanding situations. These bars will take punishment and never let you down • 60W/4,200 LM (3W per diode) • Combination Flood/Spot Optics • 5.7 Amps • 50,000 hour lifetime • 6,500 Kelvin color • 12V-32V capable • IP68 Waterproof Rated • Bar Measures 12" End to End w/ Brackets • Lens Measures 10" End to End • Mount to Mount measurement is 15" • Super efficient LED driver • Special optics improve light projection • Perfect for off-road, emergency, and public use • Lifetime Warranty

Est. Labor	Hours		
Gross Weight	5.20	Width	13.50
Net Weight	5.20	Height	5.25
DIM Weight	2.68	Depth	5.25

Kelvin (ColorTemperature)

6,500K

Universal or Vehicle Specific

Universal

Made In

China

Warranty

Lifetime

Lumens

4,200lm

Beam Pattern

Combo

Prop 65 WARNING: This product can expose you to chemicals, which are known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov