



SKU # RS-EE-RED

Part # 1004392

Description

Quarter Size Marker LED Custom Light (Red) with Mounting Back Bolt

Categories

Powersports, Auto Interior & Exterior, Motorcycle, Interior/Exterior Accent LED, Motorcycle Lighting

Sub-Categories

Eagle Eye Custom LEDs, Eagle Eye Custom LEDs, LED Engine Accent Lighting Hi Temp, Eagle Eyes and Courtesy Lights, Custom Lighting

UPC 817363013956

Unit of Measure PR

Related Skus:

Cross Sell Skus:

Condition

New

Manufacturer

Race Sport Lighting

EZ Category

LED Accent Lighting

Harmonization Code

8512.20.2080

Universal

YES

Life Expectancy

SEMA Product Interior Accent Light

Part Type ID 18826

Reverse Polarity

Interior Accent Light

Operating Voltage

Current Draw

Wattage

Chip Type

IP Rating

LUX

Kelvin (ColorTemperature)

Red

Universal or Vehicle Specific

Universal

Made In

China

Warranty

1 year

Lumens

Beam

Pattern



Product Information

Add luxury and style to your car and increase your visibility 300% with Race Sport Eagle Eyes! These super bright LEDs project crisp, clear colors, perfect in front or rear bumpers for DRLs, taillights, or reverse lights. The custom applications for our Eagle Eyes, however, are endless. • 12 Volt Applications • Sold In Pairs • 3 Watts • Applications: DRLs, Taillights, Custom lighting • Colors available: Hyper White, Yellow, Green, Red and Blue • 1 Year Warranty

Est. Labor

Hours

Gross Weight

0.10

Width

3.00

Net Weight

0.10

Height

1.00

DIM Weight

0.11

Depth

5.00

Prop 65 WARNING: This product can expose you to chemicals, which are known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

www.racesportinc.com