



## SKU # RS-EE-WHITE

Part # 1004393

### Description

Quarter Size Marker LED Custom Light (White) with Mounting Back Bolt

### Categories

Powersports, Auto Interior & Exterior, Motorcycle, Interior/Exterior Accent LED, Motorcycle Lighting

### Sub-Categories

Eagle Eye Custom LEDs, Eagle Eye Custom LEDs, LED Engine Accent Lighting Hi Temp, Eagle Eyes and Courtesy Lights, Custom Lighting

UPC 817363013918

Unit of Measure PR

### Related Skus:

### Cross Sell Skus:

### Condition

New

### Manufacturer

Race Sport Lighting

### EZ Category

LED Accent Lighting

### Harmonization Code

8512.20.2080

### Universal

YES

### Life Expectancy

SEMA Product Interior Accent Light

Part Type ID 18826

### Reverse Polarity

Interior Accent Light

### Operating Voltage

### Current Draw

### Wattage

### Chip Type

### IP Rating

### LUX

### Kelvin (ColorTemperature)

White

### Universal or Vehicle Specific

Universal

### Made In

China

### Warranty

1 year

### Lumens

### Beam Pattern



### Product Information

Add luxury and style to your car and increase your visibility 300% with Race Sport Eagle Eyes! These super bright LEDs project crisp, clear colors, perfect in front or rear bumpers for DRLs, taillights, or reverse lights. The custom applications for our Eagle Eyes, however, are endless. • 12 Volt Applications • Sold In Pairs • 3 Watts • Applications: DRLs, Taillights, Custom lighting • Colors available: Hyper White, Yellow, Green, Red and Blue • 1 Year Warranty

### Est. Labor

Hours

### Gross Weight

0.10

### Width

3.00

### Net Weight

0.10

### Height

1.00

### DIM Weight

0.11

### Depth

5.00

Prop 65 WARNING: This product can expose you to chemicals, which are known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to [www.P65Warnings.ca.gov](http://www.P65Warnings.ca.gov)

[www.racesportinc.com](http://www.racesportinc.com)