



SKU # RS-T10-B-5050

Part # 1004822

Description

T10 5050 LED 5 Chip Bulbs (Blue) (Pair)



Categories

Powersports, Agricultural, Motorcycle, Auto Interior & Exterior, LED Replacement Bulbs

Sub-Categories

Professional Series 5050 LED Replacement Bulbs, Professional Series 5050 LED Replacement Bulbs, Professional Series 5050 LED Replacement Bulbs, LED Replacement Bulbs, 5050 Series LED Replacement Bulbs

UPC 811712020121

Unit of Measure PR

Related Skus:

Cross Sell Skus:

Condition

New

Manufacturer

Race Sport Lighting

EZ Category

5050 LED Replacement Bulbs

Est. Labor

Hours

Gross Weight

0.10

Width

2.25

Net Weight

0.10

Height

4.00

DIM Weight

0.49

Depth

7.50

Harmonization Code

8512.20.2080

Universal

YES

Life Expectancy

SEMA Product License Plate Light

Part Type ID 2816

Reverse Polarity

License Plate Light

Operating Voltage

12-24VDC

Current Draw

Wattage

Chip Type

IP Rating

LUX

Kelvin (ColorTemperature)

Blue

Universal or Vehicle Specific

Universal

Made In

China

Warranty

1 year

Lumens

Beam Pattern

Prop 65 WARNING: This product can expose you to chemicals, which are known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov