



## SKU # RS-T15-W-5050

Part # 1004840

### Description

T15 5050 LED 9 Chip Bulbs (White) (Pair)



### Categories

Jeep, Powersports, Motorcycle, Agricultural, Auto Interior & Exterior, LED Replacement Bulbs

### Sub-Categories

LED Replacement Bulbs, Professional Series 5050 LED Replacement Bulbs, Professional Series 5050 LED Replacement Bulbs, Professional Series 5050 LED Replacement Bulbs, LED Replacement Bulbs, 5050 Series LED Replacement Bulbs

UPC 811712020367

Unit of Measure PR

### Related Skus:

### Cross Sell Skus:

### Condition

New

### Manufacturer

Race Sport Lighting

### EZ Category

5050 LED Replacement Bulbs

### Est. Labor

Hours

### Gross Weight

0.20

### Width

5.00

### Net Weight

0.20

### Height

3.00

### Harmonization Code

8512.20.2080

### Universal

YES

### Life Expectancy

### DIM Weight

0.13

### Depth

1.25

SEMA Product License Plate Light

Part Type ID 2816

### Reverse Polarity

License Plate Light

### Operating Voltage

12-24VDC

### Current Draw

### Wattage

### Chip Type

### IP Rating

### LUX

### Kelvin (ColorTemperature)

White

### Universal or Vehicle Specific

Universal

### Made In

China

### Warranty

1 year

### Lumens

### Beam

### Pattern

Prop 65 WARNING: This product can expose you to chemicals, which are known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to [www.P65Warnings.ca.gov](http://www.P65Warnings.ca.gov)

[www.racesportinc.com](http://www.racesportinc.com)