

EYE & EYE ROUNDUP® ROUNDSLINGS

Eye & Eye RoundUp™ RoundSlings are ideal where abrasion to the sling body is a problem. A tough, abrasion resistant sleeve is sewn to the body forming a loop at each end. They may be used in a vertical, choker or basket hitch.

EYE AND EYE ROUNDSLING CAPACITY CHART

Colour	Part Number	Vertical	Chiker	Basket	Minimum Length	Body Width	Approx. WT / FT
PURPLE	EER1	2600	2100	5200	3'	2.25"	0.4 LB
GREEN	EER2	5300	4200	10600	3'	2.50"	0.5 LB
YELLOW	EER3	8400	6700	16800	4'	2.50"	0.6 LB
TAN	EER4	10600	8500	21200	4'	3.50"	0.7 LB
RED	EER5	13200	10600	26400	5'	3.50"	1.0 LB
WHITE	EER6	16800	13400	33600	7'	3.50"	1.1 LB
BLUE	EER7	21200	17000	42400	7'	4.25"	1.6 LB
ORANGE	EER8	25000	20000	50000	7'	5"	1.8 LB
ORANGE	EER9	31000	24800	62000	7'	6"	2.2 LB
ORANGE	EER10	40000	32000	80000	7'	6.5"	2.8 LB
ORANGE	EER11	53000	42400	106000	8'	7"	3.6 LB
ORANGE	EER12	66000	52800	132000	10'	8"	4.5 LB
ORANGE	EER13	90000	72000	180000	10'	9"	6.1 LB
ORANGE	EER14	100000	82000	200000	10'	10.4"	7.1 LB

HOW TO ORDER:

Part Number and Length
(Sling Length: Bearing Point to Bearing Point)

Example: EER2 X 20 FT

LARGER SIZES AVAILABLE



**Before ordering slings that are going to be used in a chemically active environment, contact Cargo Lift® Customer Service, to recommend the right sling for the right usage.*

