

POWERING YOUR life.

#> Model 100882

UPC 817198023618

∑★ Warranty 2 Years

## 9.5"/24.1cm Tilling Width 43cc, 2 Cycle Engine





4 HARDENED-STEEL Tines



ADJUSTABLE
Tilling Depth



BIDIRECTIONAL SHREDDING

## **Teatures**

7 in. (17.8 cm) transport wheels for easier movement over varied terrain.

Powerful 43cc 2-cycle engine with bidirectional shredding tines tames the most challenging soils.

8.75 in. (22.2 cm) hardened-steel tines perfect for gardens as well as general landscaping tasks.

Adjustable tilling depth up to 6 in. (15.2 cm)

## Q Specifications

START TYPE	Recoil
ENGINE SIZE	43cc
TINE SIZE	8.75 in.
TINES QTY.	4
TILLING WIDTH	9.5 in.
TILLING DEPTH	8.75 in.
WHEEL DIAMETER	7 in.
GASOLINE CAPACITY	0.3 gal.
OIL TYPE	50:1 (2-Stroke)
EMISSIONS	EPA









Powerful performance, comfort and durability are yours with Champion's Gas Tiller Cultivator. Tackle tough tasks easily with the powerful 43cc engine. The durable 7-inch storable wheels allow easy maneuvering while you cultivate up to 6 inches deep in any type of soil.

■ Inside the box

TILLER 2-CYCLE OIL

**OPERATOR'S MANUAL** 

What You Need

GASOLINE

(!) \*Specifications, descriptions and illustrations are subject to change without notice.



