

## Air Thermometers

**Model: AT120, AT120C (Celsius)**

Magnetic or adhesive mounting, for refrigerator, freezer, indoor or outdoor use. 1¾-inch dial. Shatterproof lens. 12 per box: 4 each white, black and red.



Features	12 per box: 4 white, 4 black, 4 red
Measurement Range	-40 to +120°F/-40 to +50°C
Unit of Measure	°F/°C
Housing Material	ABS plastic
Display Material	Shatterproof lens
Display Size	1.75"/4.4 cm dial
Resolution	5°F/2°C
Mounting	Magnet and adhesive
Dimensions	7.75 W x 2.0625 H x 2.75 D (in)/19.7 W x 5.2 H x 7.0 D (cm)
Weight	7.8 oz / 221.1 g
Warranty	5-Year Limited Warranty