

Dual-Sensing Probe Thermometer/Timer

Model: DSP1-W (White), DSP1-S (Silver)

Instant food and oven temperature readings with progress display.
Long 6¾-inch stainless steel probe. 39-inch high-heat sensor cable.
Timer counts up/down to 10 hours in hours/minutes/seconds. Distinct alarms.
Programmable. Magnet or stand mounting.



Features	Programmable, dual function, dual progress display, counts up/down, big digit, overtime alert, stop and restart, counts up after zero, on/off button
Certification	WEEE, CE
Measurement Range	32 to 572°F/0 to 300°C; 10 hours by hr/min
Unit of Measure	°F/°C
Heat Resilience	Probe: 572°F/300°C, high heat sensor cable: 600°F/315°C for 3 hours
Water Resilience	Probe able to be submerge in 1 inch water for 30 minutes, not including probe-sensor cable junction
Alert/Alarm	Alert & alarm
On/Off	On/off button
Housing Material	Food-safe ABS plastic
Display Material	LCD
Display Size	1.75 W x 1.75 H (in)/4.4 W x 4.4 H (cm)
Probe Type	Thermistor
Probe Material	304 stainless steel high heat probe
Probe Length	6.75"/17.0 cm probe with 39"/1 m sensor cable
Resolution	1°F/1°C
Temperature Guide	USDA safe food temperature guide on case
Mounting	Magnet and stand
Operating Range	32 to 104°F/0 to 40°C/≤90% RH
Battery	1.5V AAA IEC LR03 alkaline battery, included
Battery Life	1 year (working 2 hours/day)
Dimensions	3 W x 7.5 H x 0.625 D (in)/7.6 W x 19.0 H x 1.6 D (cm)
Weight	4.4 oz / 124.7 g (including battery)
Warranty	5-Year Limited Warranty
Replacement Parts	AD-DSP1