

Digital Pocket Thermometer

Model: DT450X (Black), DT450X-B (Blue), DT450X-G (Green), DT450X-R (Red)

Water resistant thermistor thermometer with quick 6-second response.
Slim design fits into chef's pocket.



Features	Expanded range, data-hold, big digit, on/off button
Certification	NSF [®] Certified, WEEE, CE
Antimicrobial Protection	BioCote [®]
Measurement Range	-40 to +450°F/-40 to +230°C
Unit of Measure	°F/°C
Accuracy	±2°F
Heat Resilience	High heat
Water Resilience	IPX4: protected from water splashes from any direction
Response Time	6 second response
On/Off	On/off button
Auto-off	Auto-off after 10 minutes
Housing Material	Food-safe ABS
Display Material	LCD
Display Size	0.9375 W x 0.5 H (in)/2.4 W x 1.3 H (cm)
Probe Type	Thermistor
Probe Material	304 stainless steel
Probe Length	2.75"/7.0 cm stem
Probe Diameter	2.5 mm reduced tip
Resolution	0.1°F/0.1°C
Casing	Sheath
Temperature Guide	USDA safe food temperature guide on thermometer
Mounting	Pocket clip
Operating Range	32 to 104°F/0 to 40°C/≤90% RH
Battery	1.5V IEC LR44 button alkaline, included
Battery Life	Typically 18 hours, continuous use
Dimensions	0.75 W x 6.5 H x 0.5625 D (in)/1.9 W x 16.5 H x 1.4 D (cm)
Weight	9 oz / 25.5 g (including battery)
Warranty	5-Year Limited Warranty