

Programmable Probe Thermometer/Timer

Model: DTP482

This digital probe thermometer and timer features a dual progress display to monitor food while cooking. Preset meat/taste temperatures for easy cooking. Detachable thermistor probe and sensor cable, plus vessel clip for candy. Timer counts up or down.



Features	Preset and programmable, dual function, dual progress display, counts up/down, 24 hours by hr/min, sliding mode switch
Certification	WEEE, CE
Measurement Range	32 to 482°F/0 to 250°C; 24 hours by hr/min
Unit of Measure	°F/°C
Heat Resilience	Probe: 482°F/250°C, high heat sensor cable: 400°F/204°C for 3 hours
Water Resilience	Probe able to be submerge in 1 inch water for 30 minutes, not including probe-sensor cable junction
Alert/Alarm	Alert & alarm
Housing Material	ABS plastic
Display Material	LCD
Display Size	1.625 W x 1.25 H (in)/4.1 W x 3.2 H (cm)
Probe Type	Thermistor
Probe Material	304 stainless steel
Probe Length	5.5"/14.0 cm probe / 3'/91.4 cm sensor cable
Resolution	1°F/1°C
Temperature Guide	USDA safe food temperature guide on case
Vessel Clip	Adjustable stainless steel clip AD-P
Mounting	Magnet, stand and hang
Operating Range	32 to 104°F/0 to 40°C/≤90% RH
Battery	1.5V AAA IEC LR03 alkaline battery, included
Battery Life	1 year (working 2 hours/day)
Dimensions	2.375 W x 4.125 H x 0.75 D (in)/6.0 W x 10.5 H x 1.9 D (cm)
Weight	4.0 oz / 113.4 g (including battery)
Warranty	5-Year Limited Warranty
Replacement Parts	AD-P, AD-DTP482