

Thin Tip Thermometer

Model: DTQ450X

One of our most full-featured thermistor thermometers, with a 1.5 mm thin tip and quick 6-second response. Waterproof and field recalibratable. Easy-to-read front-facing display.



| | |
|--------------------------|--|
| Features | Data-hold, max mode, big digit, on/off button |
| Certification | NSF [®] Certified, WEEE, CE |
| Antimicrobial Protection | BioCote [®] |
| Measurement Range | -40 to +450°F/-40 to +230°C |
| Unit of Measure | °F/°C |
| Accuracy | ±2°F |
| Calibration | Field calibration |
| Water Resilience | IPX6: protected from water in powerful jets against the enclosure from any direction for 3 minutes |
| Response Time | 6 second response |
| On/Off | On/off button |
| Auto-off | Auto-off after 10 minutes |
| Housing Material | 304 stainless steel housing, 304 stainless steel stem |
| Display Material | LCD |
| Display Size | 0.875 W x 0.5 H (in)/2.2 W x 1.3 H (cm) |
| Probe Type | Thermistor |
| Probe Material | 304 stainless steel |
| Probe Length | 5"/12.7 cm stem |
| Probe Diameter | 1.5 thin tip |
| Resolution | 0.1°F/0.1°C |
| Casing | Sheath |
| Mounting | Pocket clip |
| Operating Range | 32 to 104°F/0 to 40°C/≤90% RH |
| Battery | 1.5V IEC LR44 alkaline button, included |
| Dimensions | 1.625 W x 6.125 H x 1.375 D (in)/4.1 W x 15.6 H x 3.5 D (cm) |
| Weight | 1.2 oz / 34 g (including battery) |
| Warranty | 5-Year Limited Warranty |