

Combo Probe Thermometer, Timer & Clock

Model: DTTC-W (White), DTTC-W-ES (White, Spanish), DTTC-S (Silver), DTTC-S-ES (Silver, Spanish)

This digital probe thermometer, timer and clock features a dual progress display to monitor food while cooking. Detachable thermister probe and sensor cable, plus vessel clip for candy. Counts up or down. Programmable alarm can sound at specified time or internal temperature.



Features	Triple function, upper and lower limits, dual progress display, counts up/down, big digit, clock, stop and restart, last count recall, 24 hours by min/sec, sliding mode switch, international time
Certification	WEEE, CE
Measurement Range	14 to 392°F/-10 to +200°C; 24 hours by min/sec
Unit of Measure	°F/°C
Heat Resilience	Probe: 392°F/200°C, high heat sensor cable: 400°F/204°C for 3 hours
Water Resilience	Probe able to be submerge in 1 inch water for 30 minutes, not including probe-sensor cable junction
Alert/Alarm	Alert & alarm
Housing Material	ABS plastic
Display Material	LCD
Display Size	1.625 W x 1.25 H (in)/4.1 W x 3.2 H (cm)
Probe Type	Thermistor
Probe Material	304 stainless steel
Probe Length	5.5"/14.0 cm probe / 3'/91.4 cm sensor cable
Resolution	0.1°F/0.1°C
Temperature Guide	USDA safe food temperature guide on case
Vessel Clip	Adjustable stainless steel clip AD-P
Mounting	Magnet and stand
Operating Range	32 to 104°F/0 to 40°C/≤90% RH
Battery	1.5V AAA IEC LR03 alkaline battery, included
Battery Life	1 year (working 2 hours/day)
Dimensions	2.625 W x 4.75 H x 0.75 D (in)/6.7 W x 12.1 H x 1.9 D (cm)
Weight	4.6 oz / 130.4 g (including battery)
Warranty	5-Year Limited Warranty
Replacement Parts	AD-P, AD-DTTC