

# Oven Thermometer

## Model: EOT1

Monitors exact oven temperatures 100 to 600°F/50 to 300°C. 304 stainless steel housing and laboratory glass lens. Stands or hangs in oven.



Features	Target range indication
Measurement Range	100 to 600°F/50 to 300°C
Unit of Measure	°F/°C
Heat Resilience	Ovenproof
Housing Material	304 stainless steel housing
Display Material	Durable laboratory glass lens
Display Size	1.625"/4.1 cm dial
Resolution	25°F/10°C
Mounting	Stand or hangs in oven
Dimensions	2.375 W x 3.625 H x 1.25 D (in)/6.0 W x 9.2 H x 3.2 D (cm)
Weight	1.6 oz / 45.4 g
Warranty	5-Year Limited Warranty