

Grill Surface Thermometer

Model: GTS800X

Monitors high heat grill surface temperatures 100 to 800°F/40 to 425°C.
430 stainless steel housing and laboratory glass lens. Color-coded scale.
Tabs for easy pickup.



Features	Place directly on surface/grill; tabs for easy pick-up; target range indication; color-coded scale
Certification	NSF [®] Certified
Measurement Range	100 to 800°F/40 to 425°C
Unit of Measure	°F/°C
Heat Resilience	High heat
Housing Material	430 stainless steel housing
Display Material	Durable laboratory glass lens
Display Size	2.25"/5.7 cm dial
Resolution	10°F/5°C
Mounting	Stand or hangs in oven
Dimensions	2.5 W x 2.5 H x 0.75 D (in)/6.4 W x 6.4 H x 1.9 D (cm)
Weight	2.5 oz / 70 g
Warranty	5-Year Limited Warranty