

## Infrared Gun

### Model: IN1022

At the push of a button, it provides a surface or ambient temperature reading in just one second. Measures up to 1,000 degrees and shows maximum, minimum, difference and average temperatures, with a lock for continuous scanning. Distance:spot ratio of 12:1.



Features	Memory, maximum, minimum, difference, average and lock for continuous scanning, backlit, data-hold, one-button operation, battery status indication
Certification	WEEE, CE
Measurement Range	-76 to +1022°F/-60 to +550°C
Unit of Measure	°F/°C
Accuracy	±2.7°F/±1.5°C
Distance:Spot	12:1
Target Illumination	8-beam laser target illumination
Emissivity	0.1~1, Step 0.01
Spectral Response	5.5~14 μm
Response Time	1 second response
Auto-off	Auto-off after 60 seconds
Housing Material	ABS plastic
Display Material	LCD
Display Size	0.875 W x 1.0 H (in)/2.2 W x 2.5 H (cm)
Resolution	0.1°F/0.1°C
Operating Range	32 to 122°F/0 to 50°C
Battery	Two 1.5V AAA IEC LR03 alkaline batteries, included
Battery Life	Typically 14 hours and 18 minutes, continuous use
Dimensions	1.625 W x 5.875 H x 4.5 D (in)/3.9 W x 7.68 H x 1.93 D (cm)
Weight	5.9 oz / 167.3 g (including battery)
Warranty	1-Year Limited Warranty