

## Cooking Thermometer

### Model: IR220

Our most basic bimetal model. Safe for commercial dishwashers and field calibration. Temperature guide on ABS sheath. Shatterproof lens. 1-inch magnified dial.



Features	1"/2.5 cm magnified dial
Measurement Range	60 to 220°F
Unit of Measure	°F
Accuracy	±2°F
Calibration	Field calibration
Water Resilience	Safe for commercial dishwashers
Response Time	15 second response (approximate)
Housing Material	304 stainless steel
Display Material	Shatterproof lens
Display Size	1"/2.5 cm magnified dial
Probe Type	Bimetal
Probe Material	304 stainless steel
Probe Length	5"/12.7 cm stem
Probe Diameter	3 mm tip
Resolution	2°F
Casing	Sheath
Temperature Guide	USDA safe food temperature guide on sheath
Mounting	Pocket clip
Dimensions	1 W x 5.5 H x 1 D (in)/2.5 W x 14.0 H x 2.5 D (cm)
Weight	0.6 oz / 17 g
Warranty	5-Year Limited Warranty
Optional Accessories	AD-F