

Beverage & Frothing Thermometer – 6.5" Stem

Model: IRB220-F-6.5, IRB220-F-6.5-C (Celsius)

Color-coded target range indication. 1½-inch dial. 6½-inch stem.
Durable 304 stainless steel. Exclusive adjustable stainless steel vessel clip
for large pitchers. Calibration tool and pocket clip on ABS sheath with BioCote[®].
Safe for commercial dishwashers.



Features	Target range indication
Certification	NSF [®] Certified
Antimicrobial Protection	BioCote [®]
Measurement Range	0 to 220°F/-18 to +104°C
Unit of Measure	°F/°C
Accuracy	±2°F
Calibration	Field calibration
Water Resilience	Safe for commercial dishwashers
Response Time	15 second response (approximate)
Housing Material	304 stainless steel
Display Material	Shatterproof lens
Display Size	1.5"/3.8 cm dial
Probe Type	Bimetal
Probe Material	304 stainless steel
Probe Length	6.5"/16.5 cm stem
Probe Diameter	3 mm tip
Resolution	2°F/1°C
Vessel Clip	Adjustable stainless steel clip AD-N
Casing	Sheath
Mounting	Pocket clip
Dimensions	1.5 W x 7 H x 1.5 D (in)/3.8 W x 17.8 H x 3.8 D (cm)
Weight	1.1oz / 31.2 g
Warranty	5-Year Limited Warranty
Optional Accessories	AD-N