

Ovenproof Meat Thermometer – Glow

Model: IRM200-GLOW

Specialized thermometer with glow-in-the-dark dial and easy-to-read dual scale for meat and poultry. Glass lens makes it ovenproof. Waterproof and field calibration. Extra large 2-inch dial.



Features	Glow in the dark dial; target range indication; target marker
Certification	NSF [®] Certified
Measurement Range	120 to 200°F/50 to 100°C
Unit of Measure	°F/°C
Accuracy	±2°F
Calibration	Boil test field calibration
Heat Resilience	Ovenproof
Water Resilience	Safe for commercial dishwashers
Response Time	25 second response (approximate)
Housing Material	304 stainless steel
Display Material	Durable laboratory glass lens
Display Size	Extra large 2"/5.1 cm dial
Probe Type	Bimetal
Probe Material	304 stainless steel
Probe Length	5"/12.7 cm stem
Probe Diameter	3 mm tip
Resolution	2°F/1°C
Temperature Guide	USDA safe food temperature guide on thermometer
Dimensions	2.75 W x 5.375 H x 2.75 D (in)/7.0 W x 13.7 H x 7.0 D (cm)
Weight	2.4 oz / 68 g
Warranty	5-Year Limited Warranty