

# Beverage & Frothing Thermometer – 7" Stem

**Model: IRTL220**

Color-coded target range indication. 1¾-inch dial. 7-inch stem.

Durable 304 stainless steel. Exclusive adjustable stainless steel vessel clip for large pitchers. Calibration tool and pocket clip on ABS sheath with BioCote<sup>®</sup>. Safe for commercial dishwashers.



|                          |  |
|--------------------------|--|
| Features                 | Target range indication                                  |
| Certification            | NSF <sup>®</sup> Certified                               |
| Antimicrobial Protection | BioCote <sup>®</sup>                                     |
| Measurement Range        | 0 to 220°F/-18 to +104°C                                 |
| Unit of Measure          | °F/°C  |
| Accuracy                 | ±2°F   |
| Calibration              | Field calibration  |
| Water Resilience         | Safe for commercial dishwashers                          |
| Response Time            | 15 second response (approximate)                         |
| Housing Material         | 304 stainless steel                                      |
| Display Material         | Shatterproof lens  |
| Display Size             | 1.75"/4.4 cm dial  |
| Probe Type               | Bimetal  |
| Probe Material           | 304 stainless steel                                      |
| Probe Length             | 7"/17.8 cm stem  |
| Probe Diameter           | 3 mm tip   |
| Resolution               | 2°F/1°C  |
| Vessel Clip              | Adjustable stainless steel clip AD-N                     |
| Casing                   | Sheath   |
| Mounting                 | Pocket clip  |
| Dimensions               | 1.75 W x 7.5 H x 1.75 D (in)/4.4 W x 19.0 H x 4.4 D (cm) |
| Weight                   | 1.5 oz / 42.5 g  |
| Warranty                 | 5-Year Limited Warranty                                  |
| Optional Accessories     | AD-N   |