

Large Dial Cooking Thermometer

Model: IRXL220

Large 1¾-inch dial. 5-inch stem. Safe for commercial dishwashers and field calibration. Calibration wrench and pocket clip on ABS sheath with BioCote[®]. Shatterproof lens.



Features	1.75"/4.4 cm dial
Certification	NSF [®] Certified
Antimicrobial Protection	BioCote [®]
Measurement Range	0 to 220°F
Unit of Measure	°F
Accuracy	±2°F
Calibration	Field calibration
Water Resilience	Safe for commercial dishwashers
Response Time	15 second response (approximate)
Housing Material	304 stainless steel
Display Material	Shatterproof lens
Display Size	1.75"/4.4 cm dial
Probe Type	Bimetal
Probe Material	304 stainless steel
Probe Length	5"/12.7 cm stem
Probe Diameter	3 mm tip
Resolution	2°F
Casing	Sheath
Mounting	Pocket clip
Dimensions	1.75 W x 5.5 H x 1.75 D (in)/4.4 W x 14.0 H x 4.4 D (cm)
Weight	0.8 oz / 22.7 g
Warranty	5-Year Limited Warranty
Optional Accessories	AD-F