

## Candy & Deep Fry Thermometer

**Model: IRXL400, IRXL400C (Celsius)**

The large 1¾-inch easy-to-read display features color-coded target range indicators. The exclusive adjustable stainless steel vessel clip makes candy-making and deep-frying easy. Stands out for its easy recalibration, with the calibration tool conveniently located on the sheath.



Features	Target range indication, color-coded scale
Certification	NSF <sup>®</sup> Certified
Antimicrobial Protection	BioCote <sup>®</sup>
Measurement Range	IRXL400: 100 to 400°F / IRXL400C: 34 to 210°C
Unit of Measure	IRXL400: °F / IRXL400C: °C
Accuracy	±2°F
Calibration	Field calibration
Water Resilience	Safe for commercial dishwashers
Response Time	15 second response (approximate)
Housing Material	304 stainless steel
Display Material	Shatterproof lens
Display Size	1.75"/4.4 cm dial
Probe Type	Bimetal
Probe Material	304 stainless steel
Probe Length	7"/17.8 cm stem
Probe Diameter	3 mm tip
Resolution	IRXL400: 5°F / IRXL400C: 2°C
Vessel Clip	Adjustable stainless steel clip AD-N
Casing	Sheath
Mounting	Pocket clip
Dimensions	1.75 W x 7.5 H x 1.75 D (in)/4.4 W x 19.0 H x 4.4 D (cm)
Weight	1.5 oz / 42.5 g
Warranty	5-Year Limited Warranty
Optional Accessories	AD-N