

# Meat/Yeast Thermometer

## Model: MYT200

An old favorite. Ovenproof and dishwasher safe.  
Temperature guide on thermometer.



Features	Dual scale, target range indication
Measurement Range	100 to 200°F/38 to 93°C
Unit of Measure	°F/°C
Heat Resilience	Ovenproof
Water Resilience	Safe for commercial dishwashers
Response Time	25 second response (approximate)
Housing Material	304 stainless steel
Display Material	Durable laboratory glass column
Display Size	2.125 W x 3.125 H (in)/5.4 W x 7.9 H (cm)
Probe Type	Non-mercuric glass column in stainless steel
Probe Material	304 stainless steel
Probe Length	4"/10.2 cm stem
Probe Diameter	3 mm tip
Resolution	10°F/5-6°C
Temperature Guide	USDA safe food temperature guide on thermometer
Dimensions	2.125 W x 7.5 H x 0.25 D (in)/5.4 W x 19.0 H x 0.6 D (cm)
Weight	1.3 oz / 36.9 g
Warranty	5-Year Limited Warranty