

Direct Entry 2-Alarm Timer

Model: TM30

Loud audio or silent vibration alarm, with direct entry convenience.
Counts up or down in hours/minutes/seconds, up to 10 hours. Large digits.
Pocket clip, magnet, stand, or loop mounting.



Features	Counts up/down, big digit, direct entry, loud alarm, long alarm, audio/vibrate, stop and restart, last count recall, counts up after zero, sliding mode switch
Certification	WEEE, CE
Measurement Range	10 hours by hr/min/sec
Unit of Measure	hour/minute/second
Alert/Alarm	≥70 dB alarm for 1 minute, then counts up
Housing Material	Brushed stainless steel finish, ABS plastic
Display Material	LCD
Display Size	1.875 W x 0.75 H (in)/4.8 W x 1.9 H (cm)
Resolution	1 second
Mounting	Pocket clip, magnet, stand and loop
Operating Range	32 to 104°F/0 to 40°C/≤90% RH
Battery	1.5V AAA IEC LR03 alkaline battery, included
Battery Life	6 months
Dimensions	2.5 W x 3.0 H x 1.0 D (in)/6.4 W x 7.6 H x 2.5 D (cm)
Weight	2.6 oz / 73.1 g (including battery)
Warranty	5-Year Limited Warranty