



- 1.
- 2.

## **Brentwood TS-345R Stainless Steel 4 Slice Toaster Oven, Red [TS-345R]**

The powerful 800w Brentwood TS-345R Stainless Steel 4 Slice Toaster Oven can toast, broil and bake an array of foods. Adjustable temperature ranges 50 to 450 degrees. Choose between the 15 minute timer with auto shut off and stay on functions. Two rack positions and two heating elements insure even toasting. Convenient crumb tray. Includes food tray and wire rack.

- Toast, Bake and Broil
- 50-450F Adjustable Temperature
- 15 Minute Timer with Auto Shut Off
- Stay On function
- 2 Rack Positions
- 2 Piece Quartz Heating Element
- Zinc Coated Chamber
- Crumb Tray
- Power Indicator Light
- Includes Food tray and Wire Rack
- Color: Metallic Red
- Power: 800w
- Approval Code: cETL \_br / \_

Item UPC Code: 1 81225 00345 5

Item Weight: 5.2 lbs.

Item Dimensions (LxWxH): 14.5 x 9.5 x 8.5 inches \_br / \_

Colored Box Dimensions: 15.5 x 12 x 9 inches

Case Pack: 4

Master Case UPC Code: 1 81225 71345 3

Case Pack Weight: 32 lbs.

Case Pack Dimensions: 24.5 x 16 x 19 inches

Availability: Please Call or Email Us for Details