

4 series S425



Sizes Available

- 43" Class** **49" Class**
- 50" Class** **55" Class**
- 65" Class** **75" Class**

Key Features:
Striking 4K Ultra HD with High Dynamic Range
4K Creative Pro Upscaling
Simple, Intuitive Interface
Dual-band Wi-Fi & Ethernet Port



Your Easiest Way to Endless Entertainment

The 4-Series 4K TCL Roku TV delivers stunning Ultra HD picture quality with four times the resolution of Full HD for enhanced clarity and detail, as well as the most streaming channels of any 4K TV. To make the most of all this content, high dynamic range (HDR) technology delivers bright and accurate colors for a lifelike viewing experience. In addition, your favorite HD shows, movies, and sporting events are upscaled to near Ultra HD resolution with 4K upscaling. The simple, intuitive interface allows seamless access to over 500,000 streaming movies and TV episodes, your cable box, Blu-ray player, gaming console, and other devices without flipping through inputs or complicated menus.

The 4K Spotlight channel makes it easy to find available 4K content across popular streaming channels. With a super-simple remote and both a dual-band Wi-Fi connection and Ethernet port, it is fast and easy to access your favorite content. Connect all your favorite devices with the 3 HDMI inputs or cast content from your smartphone or tablet with the free mobile app. The built-in TV tuner with available smart program guide makes this the ultimate cord-cutting TV as it also gives you the ability to access free, over-the-air HD content. With Ultra 4K HD resolution and over 5,000 streaming channels featuring the best selection of music, sports, news, and more, the 4K TCL Roku TV is your easiest way to endless entertainment.

Product Highlights			
<p>Striking 4K UHD Picture Performance with High Dynamic Range</p> <p>Ultra HD resolution with HDR offers exceptional clarity and detail.</p>	<p>HD → UHD</p> <p>4K Creative Pro Upscaling</p> <p>View your favorite HD content in near 4K quality.</p>	<p>Simple, Intuitive Interface</p> <p>Seamless access to over 500,000 streaming movies & TV episodes.</p>	<p>802.11ac Dual-band Wi-Fi & Ethernet Port</p> <p>Fast and easy access to your favorite content.</p>



TCL 4-SERIES	
Model	43S425 / 49S425 / 50S425 / 55S425 / 65S425 / 75S425
Screen Class	43" / 49" / 50" / 55" / 65" / 75"
Viewable Display Size	42.5" / 48.5" / 49.5" / 54.6" / 64.5" / 74.5"
Description	Smart Value LED 4K TV / HDR 4K TV
UPC	
43S425: 846042010030	49S425: 846042010054
50S425: 846042010078	55S425: 846042010108
65S425: 846042010139	75S425: 846042010290
Wi-Fi	802.11ac 2x2 Dual Band (support 2.4GHz & 5GHz)
Processor Type	CPU: Dual-core / GPU: Dual-core
DISPLAY	
Clear Motion Index	120Hz CMI
Panel Resolution	3840 x 2160
Resolution	UHD
Display Colors	1.07 billion
High Dynamic Range Format	HDR10
FEATURES	
Advanced PQ Setting with Mobile App	Yes
Control Buttons	Power/Menu, ←, →/one button
Multilingual On-Screen-Display	English, Spanish, French, German
Closed Caption	Yes
Parental control (V-Chip)	Yes
Accessible Menu System (CVAA)	Yes
AUDIO	
Audio Power (Watts)	2 Channel x 8W; 75" 2 Channel x 10W
Audio Passthrough	Dolby Digital Plus
Dolby Processing	Dolby Digital; 75" Dolby MS12B

CONNECTED TV	
Smart Platform	Roku
SIGNAL FORMAT CAPABILITY	
Tuner Type	ATSC / NTSC / Clear QAM
CONNECTIONS—Inputs/Outputs	
AV input	Composite Video + L&R Audio In
Audio output (RCA)	No
VGA	No
RF Input (NTSC, ATSC)	1
Ethernet	1
USB	1 USB2.0
HDMI	3 HDMI 2.0 w/HDCP 2.2 (1 ARC)
SPDIF Digital Audio Optical	1
Audio output Headphone	1
YPbPr (Component Video) Input	No
ENERGY INFORMATION	
Energy Star	No
Energy Guide	\$12; \$14; \$15; \$18; \$22; \$36
Power Consumption	85W; 100W; 105W; 125W; 145W; 260W
Standby Power	<0.5W
ACCESSORIES (INCLUDED)	
Warranty Info / Quick Start Guide (QSG)	1 / 1 (English)
Remote Control	Roku TV RC282; 75" RC280
Remote Control Battery	Two "AAA"
WARRANTY	
1 year limited warranty	

* All Product Specifications Are Subjected to Change Without Notice.

PRODUCT & PACKAGE INFO	43"	49"	50"	55"	65"	75"
Product Size (WxHxD) with stand	38.2" x 24.5" x 7.6"	43.5" x 27.6" x 8.7"	44.1" x 28.0" x 8.0"	49.0" x 30.6" x 8.0"	57.3" x 36.0" x 11.8"	66.1" x 40.7" x 15.9"
Product Size (WxHxD) without stand	38.2" x 22.4" x 3.0"	43.5" x 25.4" x 3.1"	44.1" x 25.7" x 3.2"	49.0" x 28.4" x 3.1"	57.3" x 33.3" x 3.1"	66.1" x 38.0" x 3.5"
Stand Separation Distance	32.4"	37.3"	39.6"	42.3"	51.3"	62.3"
Product Weight with stand (lbs)	16.5 lbs	22.0 lbs	23.6 lbs	27.1 lbs	39.7 lbs	75.0 lbs
Product Weight without stand (lbs)	16.3 lbs	21.6 lbs	23.1 lbs	26.7 lbs	38.8 lbs	73.9 lbs
Package Size (WxHxD) (inches)	45.1" x 26.2" x 5.2"	49.8" x 30.5" x 6.3"	49.8" x 30.5" x 6.3"	55.1" x 34.0" x 6.6"	64.8" x 39.4" x 8.4"	72.8" x 46.1" x 11.2"
Total Package Weight (lbs)	23.1 lbs	32.0 lbs	33.5 lbs	39.2 lbs	59.5 lbs	105.8 lbs
VESA MOUNTING SPECIFICATIONS						
VESA Hole Pattern	100mm (V) x 100mm (H)	200mm (V) x 200mm (H)	200mm (V) x 200mm (H)	200mm (V) x 200mm (H)	400mm (V) x 200mm (H)	300mm (V) x 300mm (H)
Screw Size	M6 x 12	M6 x 12	M6 x 12	M6 x 12	M6 x 12	M6 x 25
BASE STAND SPECIFICATIONS						
Screw Size (Qty)	ST4 x 25 (4)	M5 x 25 (4)	M5 x 25 (4)	M5 x 25 (4)	M5 x 25 (4)	M5 x 20 (4)



Already one of the world's best-selling TV brands, TCL (The Creative Life) is now one of the fastest-growing consumer electronics brands in North America. Founded over 30 years ago, TCL prides itself on delivering high-quality products featuring stylish designs and the latest technology.