


Bulldog Commercial Hardware 6900 Series ANSI/BHMA Grade-2 Heavy Duty Interconnect Specifications



INTERCONNECT SPECIFICATIONS		INTERCONNECT FUNCTIONS		
ANSI/BHMA	Grade-2.			
Latch	2-3/8" backset, 1" round corner narrow faceplate std. 2-3/4" square corner optional.		AL6920 Passage 1-Point Locking	1
Strikes	Deadbolt: PT-DS06 2-3/4" RCS std. Lever: PT-LS16 full lip RCS std.			
Cylinder	5 pin KW1 std. "C" optional.	, ,		
Door Prep	Edge bore 1", latch mortise 1"x 2-1/4", cross bores 2-1/8", 4" Center to Center.		AL6941	Key or inside push button locks
Door Thickness	Min 1-3/8", Max 1-3/4".	9	Entry	both levers. Turning inside lever unlocks both levers and the dead-
Handing	Non-Handed Design.		2-point	bolt simultaneously. Deadbolt also unlocked with key or by rotating
U.L.	3 hour, U.L. Labeled Fire Rated.		Locking	interior thumb turn.
Warranty	Lifetime mechancial, 2 year finish.			