



Mini Trackball Keyboard

www.adesso.com



The Adesso Mini Trackball Keyboard provides you with optimum control of your computer without the need of a mouse. The integrated trackball and mouse buttons provide you with everything you need to navigate your screen quickly and efficiently. The keyboard's trackball delivers superior precision and smooth motion with no maintenance or cleaning required. This 11.75" Adesso Mini Trackball Keyboard is perfect for compact spaces like small office cubicles, home offices and kiosks.



Built-in Optical Trackball



Compact Size



Membrane Switch

■ Built-In Optical Trackball

The integrated trackball eliminates the need for a mouse and saves valuable desk space, with its 800 DPI resolution the optical trackball provides superior accuracy and smooth motion requiring minimal hand movement and no maintenance.

■ Compact Size

This keyboard is 11.75" wide and is designed with a Windows layout that includes an embedded numeric keypad. This keyboard is a great space saver for all environments and ideal for public workstations.

■ Membrane Keys Offer Fast Typing and a Long Lifecycle

The membrane keys offer you fast typing and a lifecycle of more than five million keystrokes.

Specifications:

Keyboard Layout	87-Key US Layout
Connection	USB
Key Type	Membrane
Cable Length	6 feet
Keyboard Dimensions	11.75 x 6.00 x 0.75" (297 x 150 x 20mm)
Switch Life	5 Million Cycles
Weight	1.1875lbs (550g)
Trackball Diameter	0.625" (15mm)
Trackball Resolution	800 DPI

Requirements:

Operating System	Windows 7/Vista/ XP, 2000 and below
Connectivity Interface	USB

Includes:

- Mini Trackball Keyboard
- Quick Start Guide

Shipping Information:

Item	Connection	UPC Code	Box Dimensions	Box Wt.	Qty/Ctn
AKB-310UB	USB	783750002813	12.50" x 8.00" x 1.5"	1.56 lbs	10/10