

## Bloom flush mount

Our LED flush mounts put ease and flexibility at your fingertips. When dimming the light fixture under 25%, only the glow ring will be activated, providing the perfect night light.



**JA8**  
CERTIFIED



Model	Size	Watts	Delivered lumens	LED lumens	CRI	Color °T	Voltage
CFR12-3K	12"	26 W	1570 lm	2300 lm	90	3000 K	120 V

**Specifications**

- Over 50,000 hours of service life
- Integrated driver
- Warm white light
- Excellent color rendering
- Superior LED performance and lifespan
- Minimal heat emission
- Frosted lens
- Edge-lit technology
- Die-cast aluminum housing
- General lighting zone turns off in the lower dimming range, back lighting stays on
- Canopy mount on 4" octagon junction box
- Suitable for dry locations
- Refer to website for dimmer compatibility
- 5-year warranty

**Finish**

- **SN** Satin Nickel
- **WH** White

**Order example**

**CFR12-3K-WH**  
CFH12-3K 12" round flush mount in a white finish

**Note**

Other Color °T and Finishes available, but may require MOQ's and longer lead times. Please contact your DALs representative for more information.

**CFR12-3K**

