

---

# LED step light

The simplicity of this design allows for the highest level of flexibility when choosing your application. Light glowing from all directions creates the perfect ambiance for every setting



Model	Watts	Delivered lumens	LED lumens	CRI	Color °T	Voltage
<b>LEDSTEP004D</b>	3 W	40 lm	285 lm	80	3000 K	120 V

**Specifications**

Die-cast aluminum housing  
 Over 50,000 hours of service life  
 Warm white light output  
 Optimized light spread  
 Low power consumption  
 Excellent color rendering  
 Superior light color consistency  
 Aesthetic profile  
 Dimmable  
 Includes a junction box approved for concrete applications  
 Suitable for wet locations  
 Refer to website for dimmer compatibility  
 Ideal operating temperature:  
 -20° to 40° C  
 5-year warranty

**Finish**

- **BK** Black
- **SG** Silver grey
- **WH** White

**Order example**

**LEDSTEP004D-WH**  
 Dimmable LEDSTEP004D step light  
 in a white finish

**Note**

Other Color °T and Finishes available, but may require MOQ's and longer lead times. Please contact your DALs representative for more information.



**LEDSTEP004D**

