

---

## LED Wall mount

Imagine being able to manually control the amount of light spread coming out from both the top and bottom of your lighting fixture. This is now possible with our LED wall mount.



Model	Watts	Delivered lumens	LED lumens	CRI	Color °T	Voltage
<b>LEDWALL001D</b>	7 W	540 lm	600 lm	90	3000 K	120 V

**Specifications**

Over 50,000 hours of service life  
 Cast aluminum construction  
 Warm white light output  
 Up and down lighting  
 Easily adjustable lighting angle from 0° to 92°  
 Low power consumption  
 Superior color consistency  
 Directional lighting  
 Integrated dimmable driver  
 Suitable for wet locations  
 Refer to website for dimmer compatibility  
 Ideal operating temperature: -20° to 40° C  
 5-year warranty

**Finish**

- **BK** Black
- **BR** Bronze
- **SG** Silver grey
- **WH** White

**Note**

Other Color °T and Finishes available, but may require MOQ's and longer lead times. Please contact your DALs representative for more information.

**Order example**

**LEDWALL001D-BK**  
 Dimmable LEDWALL001D wall mount in a black finish

**LEDWALL001D**

