LED Wall mount





This innovative sleek designed LED wall mount provides the perfect solution for your lighting needs. By adjusting the directional panels, you can create the most original effect in your setting.



| Model | Watts | Delivered lumens | LED lumens | CRI | Color °T | Voltage |
|-------------|-------|------------------|------------|-----|----------|---------|
| LEDWALL002D | 7 W | 540 lm | 600 lm | 90 | 3000 K | 120 V |

Specifications

Over 50,000 hours of service life
Cast aluminum construction
Warm white light output
Up and down lighting
Easily adjustable lighting angle
from 0° to 92°
Low power consumption
Superior color consistency
Directional lighting
Integrated dimmable driver
Suitable for wet locations
Refer to website for dimmer compatibility
Ideal operating temperature:
-20° to 40° C
5-year warranty

Finish



BK Black

Order example

LEDWALL002D-SG

Dimmable LEDWALL002D wall mount in a silver grey finish

Note

Other Color °T and Finishes available, but may require MOQ's and longer lead times. Please contact your DALS representative for more information.



LEDWALL002D

