LED Wall mount



ADA DINTERE JA8 CERTIFIED





The key design element of our LED wall mount is the removable lens. This feature allows for three distinctive styles during installation.



Model	Watts	Delivered lumens	LED lumens	CRI	Color °T	Voltage
LEDWALL-B	29 W	2100 lm	2260 lm	90	3000 K	120 V - 277 V

Specifications

 $\label{eq:continuous} \textbf{Square housing made of extruded aluminum}$

Fixture canopy made of die-cast aluminum

LED module is mounted on an aluminum heat sink to maximize heat dissipation and extend product life

The square wall mount comes with 3 optical options:

- Bright aluminum reflector that provides a 45° beam spread
- Frosted glass lens to allow a wider beam spread
- Die-caster aluminum cap to allow a down only version

Compatible with TRIAC, ELV and 0-10 V dimmers

The LED board is sealed with a clear tempered glass lens to assure weatherproof operation

Baked powder paint coat for a highly durable finish

Integrated dimmable driver

JA8 certified

ENERGY STAR certified

ADA compliant

Suitable for wet locations

Refer to website for dimmer compatibility Ideal operating temperature:

-20° to 40° C

5-year warranty

Finish

BK Black



SG Silver grey



WH White

Order example

LEDWALL-B-SG

LEDWALL-B square LED wall mount in a silver grey finish

Note

Other Color °T and Finishes available, but may require MOQ's and longer lead times. Please contact your DALS representative for more information.

LEDWALL-B



