LED Wall mount







This distinctive LED wall–mounted sconce permeates a gentle multi–directional light. Its unique geometric shape and robust design will provide a dramatic flare to any indoor/outdoor space. Ideal for residential and commercial projects, its warm splashes of light create an impressive architectural and alluring touch.



Model	Watts	Delivered lumens	LED lumens	CRI	Color °T	Voltage
LEDWALL-H	15 W	900 lm	1000 lm	90	3000 K	120 V

Specifications

-20° to 40° C

5-year warranty

Made of extruded aluminum
Fully sealed light engine
Over 50,000 hours of service life
Unique up and down lighting output
Low profile design
Warm white light output
Superior color consistency
Integrated dimmable driver
ADA compliant
Suitable for wet locations
Refer to website for dimmer compatibility
Ideal operating temperature:

Finish

BK Black

SG Silver grey

WH White

Order example

LEDWALL-H-SG

Dimmable LEDWALL-H wall mount in a silver grey finish

Note

Other Color °T and Finishes available, but may require MOQ's and longer lead times. Please contact your DALS representative for more information.



