



**DEFENDER**  
CABLE 

## 14/3 CONTRACTOR GRADE OUTDOOR EXTENSION CORDS SPECIFICATION SHEET

### PRODUCT FEATURES:

- 14/3 Contractor grade
- Ultra flexible cord in temperatures ranging -40°F to 140°F
- Abrasion and sun resistant
- Cold weather resistant
- Lighted ends w/ red indicator light
- Flame retardant
- Water resistant
- Welded hook and loop wrap for easy cord management
- Made from virgin copper for ultimate performance & quality
- 5-15 Plug and receptacle

### TECHNICAL DATA:

- Made from virgin copper
- 14 Gauge wire diameter
- 3 Conductor
- Max amps
  - 15A (25' & 50')
  - 13A (100')
- Max power:
  - 1875W (25' & 50')
  - 1625W (100')
- Receptacle:
  - 1 Outlet
- Operating temperature range
  - -40°F-140°F
- Length: 25', 50', 100'
- Water resistant
- Flame retardant
- Lighted ends
- COO: China



### STANDARDS & COMPLIANCE:

- OSHA compliant
- UL and ETL listed

### APPLICATIONS & CARE:

The contractor grade outdoor extension cord is SJTW rated and can be used in outdoor/construction settings. It is weather resistant and can operate between -40°F to 140°F. Before using, carefully observe to see if any damage is found on the wires. During use, always look to see if the red indicator light is on. When storing, keep cables in a dry cool place away from liquid or direct sunlight.

All Defender Cable cords come standard with our welded hook and loop management system.



**DEFENDER**  
CABLE 

## 14/3 CONTRACTOR GRADE OUTDOOR EXTENSION CORDS SPECIFICATION SHEET

### Packaging and Logistics Information

SKU	CORD LENGTH	JACKET COLOR	AMPS (MAX)	POWER (MAX)	CASE QTY	CASE WT	UPC
DCE-210-25	25 ft.	Orange	15 A	1875 W	12	33 lbs.	069165847875
DCE-210-45	50 ft.	Orange	15 A	1875 W	8	42 lbs	069165847882
DCE-210-65	100 ft.	Orange	13 A	1625 W	4	40 lbs.	069165847899