



**3.5 MIL EXAM GRADE/CHEMO RATED NITRILE GLOVES**  
**SINGLE USE HAND PROTECTION**  
**SPECIFICATION SHEET**



**PRODUCT FEATURES:**

- Meets the ASTM D6978 chemo rated testing
- Medical grade and are trusted by millions across the US
- Provide incredible tensile strength and elongation, with high durability and puncture resistance
- Pitted fingertips for improved grip when handling slippery objects
- Comfortable and durable for extended wear
- Beaded cuff allowing for quick donning and doffing

**TECHNICAL DATA:**

- Material:
  - 100% Nitrile
  - 100% Latex free
- Mil Thickness: 3.5 mil
- Color: Blue
- Powder Free
- Beaded Cuff
- Pitted Fingertips
- COO: China

Physical Specifications				
	Size			
	S	M	L	XL
Hand Length	7.2-7.6 in	7.4-8.0 in	7.5-8.1 in	7.6-8.2 in
Palm Width	2.8 - 2.95 in	2.95 - 3.15 in	3.15 - 3.44 in	3.44 - 3.77in
Finger Length	2.65 - 2.7 in	2.7 - 2.75 in	2.75 - 2.8 in	2.8 - 2.85 in
Palm Circumference	7 - 8 in	8 - 9 in	9 - 10 in	10 - 11 in
Cuff Thickness	1.6mil+/- 0.5mil	1.6mil+/- 0.5mil	1.6mil+/- 0.5mil	1.6mil+/- 0.5mil
Palm Thickness	3.5mil +/-0.5mil	3.5mil +/-0.5mil	3.5mil +/-0.5mil	3.5mil +/-0.5mil
Finger Thickness	5.1mils +/-0.5mil	5.1mils +/-0.5mil	5.1mils +/-0.5mil	5.1mils +/-0.5mil

**STANDARDS & COMPLIANCE:**

- 510(K) (K211808) Medical Grade
- ASTM D6319
- ASTM D6978
- EN455
- EN374
- ISO 10993 5,10 against irritation and sensitization
- Drug List
  - Carmustine (BCNU), 3.3 mg/ml (3,300 PPM) 21.5
  - Cisplatin, 1 mg/ml (1,000 ppm) >240 min
  - Cyclophosphamide (Cytoxan), 20.0 mg/ml (20,000 ppm) >240 min
  - Dacarbazine, 10 mh/ml (10,000 ppm) >240 min
  - Doxorubicin HCl 2.0 mg/ml (2000 ppm)>240 min
  - Etoposide 20.0 mg/ml (20,000 ppm)>240 min
  - Fluorouracil 50.0 mg/ml (50,000 ppm)>240 min
  - Paclitaxel, 6.0 mg/ml (6,000 ppm)>240 min
  - Thiotepa, 10.0 mg/ml (10,000 ppm) 57.7 min

**APPLICATIONS & CARE:**

These gloves are 510(k) cleared and exceed the ASTM D6139 testing performance, the nitrile gloves have incredible tensile strength and elongation, providing high durability and puncture resistance. With its pitted fingertip design, it allows for improved dexterity and grip on slippery objects. They can be used in a multitude of industries such as general examination, tattoo parlors, automotive, maintenance, food handling and cleaning.





**3.5 MIL EXAM GRADE/CHEMO RATED NITRILE GLOVES**  
**SINGLE USE HAND PROTECTION**  
**SPECIFICATION SHEET**

## Packaging and Logistics Information

SKU	SIZE	GLOVES PER BOX	BOXES PER CASE	PALLET QTY	CASE WT	UPC
DSG-ENG-01-S	S	100	10	84 CS	11.4 lbs.	069165845772
DSG-ENG-01-M	M	100	10	84 CS	11.9 lbs.	069165845789
DSG-ENG-01-L	L	100	10	84 CS	12.9 lbs.	069165845796
DSG-ENG-01-XL	XL	100	10	84 CS	13.7 lbs.	069165845802