

CHEMO RATED EXAMINATION GLOVES

The Defender Safety Chemo Examination Glove is a 510(k) Approved Medical Grade, Powder Free Nitrile Glove that can be used in a multitude of industries. The Pitted Finger Tip design allow for improved dexterity and grip on slippery objects. The Beaded Cuff offers an easy opening, quick donning and fast removal without issues. These gloves are manufactured with cGMP compliance and meets the ASTM D6319, D6978, EN455/EN ISO 374 and ISO 10993 standards. Rigorously tested, the gloves are free from holes, cytotoxin, irritant, or materials that can cause sensitization.



The Glove's material composition are Nitrile (95%), Zinc Oxide (3.4%) and Stearic Acid (1.6%). They are the ideal alternative to Vinyl and Latex Gloves. They are ambidextrous, single use and can also be used as protection in other industries such as handling food, general cleaning, tattooing, and Industrial environments.

FDA 510(k) cleared: K211708



SKU	Size	Box Quantity	Case Weight	Pallet Qty	Pallet Weight	Cubic Feet
DSG-ENG-01-S	S	10 BX (1000 PCS)	8.7 bs	64,000 PCS	557 lbs	0.74
DSG-ENG-01-M	M	10 BX (1000 PCS)	9.4 lbs	64,000 PCS	602 lbs	0.74
DSG-ENG-01-L	L	10 BX (1000 PCS)	10.1 lbs	64,000 PCS	650 lbs	0.74
DSG-ENG-01-XL	XL	10 BX (1000 PCS)	10.9 lbs	64,000 PCS	700 lbs	0.74

PRODUCT SPECIFICATIONS



Reliable protection for a wide range of Industries

- Meets ASTM D6319/D6978/EN 455/ EN ISO 374 performance levels
- Meets ISO 10993 5,10 standards against irritation and sensitization
- Ambidextrous and Fully pitted fingers for consistent grip
- Powder Free
- Medical Grade
- Chemo Rated
- FDA 510(k) cleared: K211708

PHYSICAL PROPERTIES		
CUFF THICKNESS	PALM THICKNESS	FINGER THICKNESS
1.6 mm +/- 0.5	3.5 mils +/- 0.5 mils	5.1 mils +/- 0.5 mils

SPECIFICATION	SIZE			
	S	M	L	XL
Material	Nitrile	Nitrile	Nitrile	Nitrile
Color	Blue/Violet	Blue/Violet	Blue/Violet	Blue/Violet
Hand Length	7-7.5 in	7.5-8 in	8-8.5 in	8.5-9 in
Palm Width	2.8-3.1 in	3.1-3.5 in	3.5-3.9 in	3.9-4.4 in
Finger Length	2.8-3 in	3-3.15 in	3.15-3.35 in	3.35-3.6 in
Palm Circumference	7-8 in	8-9 in	9-10 in	10-11 in
Surface	Fully Pitted	Fully Pitted	Fully Pitted	Fully Pitted

PRODUCT INFORMATION	
	Defender Safety Examination Gloves
Material	Nitrile
Color	Blue Violet
Glove Design	Powder Free, Beaded Cuff, Pitted Fingertips
Packaging	100 gloves per box 10 boxes per case 1000 gloves per case
Storage Condition	Recommended to store in a cool and dry place away from direct sunlight and hazardous environment.
Standard Compliance	ASTM D6319 / D6978 / EN 455 / EN ISO 374 / ISO 10993:5,10
Country of Origin	China
Chemo Rated Drug List:	Carmustine >240min, Cisplatin >240min, Cyclophosphamide >240min, Dacarbazine >240min, Doxorubicin HCl >240min, Etoposide >240min, Fluorouracil >240min, Paclitaxel >240min, ThioTepa 57.7min,
Available Sizes	S, M, L, XL

Defender Safety, ® and ™ are trademarks owned by Defender Safety or one of its affiliates. © 2019 Defender Safety Limited. All Rights Reserved. Neither this document nor any other statement made herein by or on behalf of Defender Safety should be construed as a warranty of merchantability or that any Defender Safety product is fit for a particular purpose. Defender Safety assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

Developed and Distributed by

Defender Safety Inc.,
30 Skyline Dr.
Plainview, NY 11803

MADE IN CHINA