



**HEXFLECTIVE REFLECTIVE SAFETY TAPE**

**SERIES HFT  
SPECIFICATION SHEET**



**PRODUCT FEATURES:**

- Highly Reflective
- Honeycomb pattern for ultimate reflective output
- Industrial grade
- Made of premium materials
- Water resistant and UV resistant
- Easy to install - Simply cut to size, peel and apply
- Strong adhesion
- Available in multiple colors

**TECHNICAL DATA:**

- Thickness:
  - .35 mm
- Size (WxL):
  - 2" x 30'
- Application Temperature
  - 39°F and above
- Operating Temperature Range
  - -40°F-220°F
- Water resistant
- UV Resistant
- COO: China

**STANDARDS & COMPLIANCE:**

- OSHA Compliant
- ADA Compliant

**APPLICATIONS & CARE:**

Incredibly strong, and versatile, our HEXFLECTIVE™ Reflective Tapes are made of premium materials and manufactured with our honeycomb pattern for ultimate reflectability and visibility. Our tapes can withstand temperatures between -40 degrees F to 220 degrees F so you can feel safe in any temperature setting. The tape can easily be applied to many different surfaces such as concrete, fiberglass, metal, plastic, or wood. Simply cut to length, peel and apply. Care is easy too - simply clean with soap and water, a light disinfectant or detergent. HEXFLECTIVE™ tape comes in a variety of colors so you can select the tape that's right for you.



## HEXFLECTIVE REFLECTIVE SAFETY TAPE

### SERIES HFT SPECIFICATION SHEET

## Packaging and Logistics Information

SKU	COLOR	SIZE (WxL)	CASE QTY	CASE WT	UPC
HFT-YHF-33	Yellow Honeycomb	2" x 30'	84 Rolls	36 lbs.	069165846335
HFT-WHF-33	White Honeycomb	2" x 30'	84 Rolls	36 lbs.	069165846342
HFT-RHF-33	Red Honeycomb	2" x 30'	84 Rolls	36 lbs.	069165846259