

1/2" Shank S & D Drills

COBALT
Fractional / Black & Gold



PACKAGING:
All sizes are individually packaged.

Series 1000C

118° SPLIT POINT / REDUCED SHANK

General purpose flute design. All sizes have a 1/2" by 2-1/4" long shank. The maximum overall length is 6" and the flute length is 3". This makes them short drills in the larger sizes and thus well suited to use in portable electric drills equipped with 1/2" chucks. They are highly effective in tough, high tensile strength materials. The 118° split point reduces thrust and eliminates walking at the drill point.



1000C

Size	Flute Length	Overall Length	1000C EDP No.
33/64"	3"	6"	1000C133
17/32"	3"	6"	1000C134
35/64"	3"	6"	1000C135
9/16"	3"	6"	1000C136
37/64"	3"	6"	1000C137
19/32"	3"	6"	1000C138
39/64"	3"	6"	1000C139
5/8"	3"	6"	1000C140
41/64"	3"	6"	1000C141
21/32"	3"	6"	1000C142
43/64"	3"	6"	1000C143
11/16"	3"	6"	1000C144
45/64"	3"	6"	1000C145
23/32"	3"	6"	1000C146
47/64"	3"	6"	1000C147
3/4"	3"	6"	1000C148

Size	Flute Length	Overall Length	1000C EDP No.
49/64"	3"	6"	1000C149
25/32"	3"	6"	1000C150
51/64"	3"	6"	1000C151
13/16"	3"	6"	1000C152
53/64"	3"	6"	1000C153
27/32"	3"	6"	1000C154
55/64"	3"	6"	1000C155
7/8"	3"	6"	1000C156
57/64"	3"	6"	1000C157
29/32"	3"	6"	1000C158
59/64"	3"	6"	1000C159
15/16"	3"	6"	1000C160
61/64"	3"	6"	1000C161
31/32"	3"	6"	1000C162
63/64"	3"	6"	1000C163
1"	3"	6"	1000C164



1000C8

No. of Pcs.	Description	EDP No.
1000C Series 1/2" Shank S&D Drill Sets		
5	9/16" - 1" BY 8ths	1000C5
8	9/16" - 1" BY 16ths	1000C8
32	STAND 1/2" - 1" BY 64ths W/DRILLS	1000C32