

# 1/2" Shank S & D Drills

**COBALT**  
Fractional / Bronze

**PACKAGING:**  
All sizes are individually packaged.

## Series 1000EC

135° SPLIT POINT / REDUCED SHANK

Expands the size range capacity of a 1/2" portable drill chuck. Common flute and overall length for minimal adjustment during tool changes. Precision ground for high degree of concentricity between shank and body diameter. Ideal for drilling in tough, high tensile strength materials. The 135° split point reduces thrust and eliminates walking at the drill point.



1000EC

Size	Flute Length	Overall Length	1000EC EDP No.
33/64"	3"	6"	1000EC133
17/32"	3"	6"	1000EC134
35/64"	3"	6"	1000EC135
9/16"	3"	6"	1000EC136
37/64"	3"	6"	1000EC137
19/32"	3"	6"	1000EC138
39/64"	3"	6"	1000EC139
5/8"	3"	6"	1000EC140
41/64"	3"	6"	1000EC141
21/32"	3"	6"	1000EC142
43/64"	3"	6"	1000EC143
11/16"	3"	6"	1000EC144
45/64"	3"	6"	1000EC145
23/32"	3"	6"	1000EC146
47/64"	3"	6"	1000EC147
3/4"	3"	6"	1000EC148
49/64"	3"	6"	1000EC149
25/32"	3"	6"	1000EC150
51/64"	3"	6"	1000EC151
13/16"	3"	6"	1000EC152
53/64"	3"	6"	1000EC153
27/32"	3"	6"	1000EC154
55/64"	3"	6"	1000EC155
7/8"	3"	6"	1000EC156

Size	Flute Length	Overall Length	1000EC EDP No.
57/64"	3"	6"	1000EC157
29/32"	3"	6"	1000EC158
59/64"	3"	6"	1000EC159
15/16"	3"	6"	1000EC160
61/64"	3"	6"	1000EC161
31/32"	3"	6"	1000EC162
63/64"	3"	6"	1000EC163
1"	3"	6"	1000EC164
1-1/32"	3"	6"	1000EC202
1-1/16"	3"	6"	1000EC204
1-3/32"	3"	6"	1000EC206
1-1/8"	3"	6"	1000EC208
1-5/32"	3"	6"	1000EC210
1-3/16"	3"	6"	1000EC212
1-7/32"	3"	6"	1000EC214
1-1/4"	3"	6"	1000EC216
1-9/32"	3"	6"	1000EC218
1-5/16"	3"	6"	1000EC220
1-11/32"	3"	6"	1000EC222
1-3/8"	3"	6"	1000EC224
1-13/32"	3"	6"	1000EC226
1-7/16"	3"	6"	1000EC228
1-15/32"	3"	6"	1000EC230
1-1/2"	3"	6"	1000EC232



1000EC5

No. of Pcs.	Description	EDP No.
<b>1000EC Series 1/2" Shank S&amp;D Drill Sets</b>		
5	9/16" - 1" BY 8ths	1000EC5
8	9/16" - 1" BY 16ths	1000EC8
32	STAND 1/2" - 1" BY 64ths W/DRILLS	1000EC32

