

Construction Reamers

HIGH SPEED STEEL
Fractional / Black Oxide



PACKAGING:
All sizes are individually packaged.

100HX Construction Reamers

STRAIGHT FLUTE / HEX NUT / BRIDGE LENGTH

Construction or Car Reamers are especially adapted for heavy duty reaming as encountered in the fabrication of structural steel assemblies. They are tapered at the point to facilitate entering of holes which are out of alignment. Available in Straight Flute, Spiral Flute, and High Spiral Flute designs with 3-Flat Straight Shanks, or with Hex Nut Shanks.



100HX

Size	Hex Dia.	Flute Length	Overall Length	100HX EDP No.
9/16"	1-1/16"	5-1/8"	6-7/8"	100HX136
5/8"	1-1/16"	6-1/8"	7-7/8"	100HX140
11/16"	1-1/16"	7-1/8"	9-1/4"	100HX144
3/4"	1-1/4"	7-3/8"	9-3/8"	100HX148
13/16"	1-1/4"	7-3/8"	9-3/8"	100HX152
7/8"	1-7/16"	7-3/8"	9-3/8"	100HX156
15/16"	1-7/16"	7-3/8"	9-3/8"	100HX160
1"	1-7/16"	7-3/8"	9-3/8"	100HX164
1-1/16"	1-5/8"	7-3/8"	9-3/8"	100HX204

Size	Hex Dia.	Flute Length	Overall Length	100HX EDP No.
1-1/8"	1-5/8"	7-3/8"	9-3/8"	100HX208
1-3/16"	1-13/16"	7-3/8"	9-3/8"	100HX212
1-1/4"	1-13/16"	7-3/8"	9-3/8"	100HX216
1-5/16"	2"	7-3/8"	10"	100HX220
1-3/8"	2"	7-3/8"	10"	100HX224
1-7/16"	2"	7-3/8"	10"	100HX228
1-1/2"	2"	7-3/8"	10"	100HX232
1-9/16"	2"	7-3/8"	10"	100HX236
1-5/8"	2"	7-3/8"	10"	100HX240

150HX Construction Reamers

STRAIGHT FLUTE / HEX NUT / CAR LENGTH

Construction or Car Reamers are especially adapted for heavy duty reaming as encountered in the fabrication of structural steel assemblies. They are tapered at the point to facilitate entering of holes which are out of alignment. Available in Straight Flute, Spiral Flute, and High Spiral Flute designs with 3-Flat Straight Shanks, or with Hex Nut Shanks.



150HX

Size	Hex Dia.	Flute Length	Overall Length	150HX EDP No.
1/2"	1-1/16"	4"	5-1/2"	150HX132
9/16"	1-1/16"	4"	5-1/2"	150HX136
5/8"	1-1/16"	4-1/2"	6"	150HX140
11/16"	1-1/16"	4-1/2"	6-3/8"	150HX144
3/4"	1-1/4"	5"	7"	150HX148
13/16"	1-1/4"	5"	7"	150HX152
7/8"	1-7/16"	5"	7"	150HX156

Size	Hex Dia.	Flute Length	Overall Length	150HX EDP No.
15/16"	1-7/16"	5"	7"	150HX160
1"	1-7/16"	5"	7"	150HX164
1-1/16"	1-5/8"	5"	7"	150HX204
1-1/8"	1-5/8"	5"	7"	150HX208
1-3/16"	1-13/16"	5"	7"	150HX212
1-1/4"	1-13/16"	5"	7"	150HX216
1-5/16"	2"	5"	7-7/8"	150HX220