

Construction Reamers

HIGH SPEED STEEL
Fractional / Black Oxide



PACKAGING:
All sizes are individually packaged.

125HX Construction Reamers

SPIRAL FLUTE / HEX NUT / BRIDGE LENGTH

Construction or Car Reamers are especially adapted for heavy duty reaming as encountered in the fabrication of structural steel assemblies. They are tapered at the point to facilitate entering of holes which are out of alignment. Available in Spiral Flute and High Spiral Flute designs with 3-Flat Straight Shanks, or with Hex Nut Shanks.



125HX

Size	Hex Dia.	Flute Length	Overall Length	125HX EDP No.
9/16"	1-1/16"	5-1/8"	6-7/8"	125HX136
5/8"	1-1/16"	6-1/8"	7-7/8"	125HX140
11/16"	1-1/16"	7-1/8"	9-1/4"	125HX144
3/4"	1-1/4"	7-3/8"	9-3/8"	125HX148
13/16"	1-1/4"	7-3/8"	9-3/8"	125HX152
7/8"	1-7/16"	7-3/8"	9-3/8"	125HX156
15/16"	1-7/16"	7-3/8"	9-3/8"	125HX160
1"	1-7/16"	7-3/8"	9-3/8"	125HX164
1-1/16"	1-5/8"	7-3/8"	9-3/8"	125HX204

Size	Hex Dia.	Flute Length	Overall Length	125HX EDP No.
1-1/8"	1-5/8"	7-3/8"	9-3/8"	125HX208
1-3/16"	1-13/16"	7-3/8"	9-3/8"	125HX212
1-1/4"	1-13/16"	7-3/8"	9-3/8"	125HX216
1-5/16"	2"	7-3/8"	10"	125HX220
1-3/8"	2"	7-3/8"	10"	125HX224
1-7/16"	2"	7-3/8"	10"	125HX228
1-1/2"	2"	7-3/8"	10"	125HX232
1-9/16"	2"	7-3/8"	10"	125HX236
1-5/8"	2"	7-3/8"	10"	125HX240