

Bridge Reamers

HIGH SPEED STEEL
Fractional / Black Oxide



PACKAGING:
All sizes are individually packaged.

4200/4250 Bridge Reamers

TAPER SHANK

Commonly used on bridgework, ship construction and structural steel fabrication where extreme accuracy of diameter is important. Reamers have pilot type points for alignment purposes and easy entry into small and off-center holes.



4200 Straight Flute



4250 Spiral Flute

Size	Point Dia.	Flute Length	Overall Length	Morse Taper	Straight Flute 4200 EDP No.	Spiral Flute 4250 EDP No.
5/16"	11/64"	4-3/8"	8-1/4"	2	420A120	425A120
11/32"	11/64"	4-3/8"	8-1/4"	2	420A122	425A122
3/8"	7/32"	4-3/8"	8-1/4"	2	420A124	425A124
13/32"	7/32"	4-3/8"	8-1/4"	2	420A126	425A126
7/16"	17/64"	4-3/8"	8-1/4"	2	420A128	425A128
15/32"	9/32"	5-1/8"	9"	2	420A130	425A130
1/2"	5/16"	5-1/8"	9"	2	420A132	425A132
17/32"	11/32"	5-1/8"	9"	2	420A134	425A134
9/16"	3/8"	5-1/8"	9"	2	420A136	425A136
19/32"	3/8"	5-1/8"	9"	2	420A138	425A138
5/8"	25/64"	6-1/8"	10"	2	420A140	425A140
21/32"	25/64"	7-1/8"	11-3/4"	3	420A142	425A142
11/16"	13/32"	7-1/8"	11-3/4"	3	420A144	425A144
3/4"	15/32"	7-3/8"	12"	3	420A148	425A148
25/32"	15/32"	7-3/8"	12"	3	420A150	425A150
13/16"	35/64"	7-3/8"	12"	3	420A152	425A152
27/32"	35/64"	7-3/8"	12"	3	420A154	425A154

Size	Point Dia.	Flute Length	Overall Length	Morse Taper	Straight Flute 4200 EDP No.	Spiral Flute 4250 EDP No.
7/8"	39/64"	7-3/8"	12"	3	420A156	425A156
29/32"	39/64"	7-3/8"	12"	3	420A158	425A158
15/16"	43/64"	7-3/8"	12"	3	420A160	425A160
31/32"	5/8"	7-3/8"	12"	3	-	425A162
1"	47/64"	7-3/8"	12"	3	420A164	425A164
1-1/32"	47/64"	7-3/8"	12"	3	420A202	425A202
1-1/16"	13/16"	7-3/8"	12"	3	420A204	425A204
1-1/8"	55/64"	7-3/8"	12"	3	420A208	425A208
1-3/16"	59/64"	7-3/8"	12"	3	420A212	425A212
1-1/4"	63/64"	7-3/8"	13"	4	420A216	425A216
1-5/16"	1-1/16"	7-3/8"	13"	4	420A220	425A220
1-3/8"	1-1/8"	7-3/8"	13"	4	420A224	425A224
1-7/16"	1-3/16"	7-3/8"	13"	4	420A228	425A228
1-1/2"	1-1/4"	7-3/8"	13"	4	420A232	425A232
1-9/16"	1-1/4"	7-3/8"	13"	4	420A236	425A236
1-5/8"	1-3/8"	7-3/8"	13"	4	420A240	425A240