



2-PIECE STAINLESS STEEL BALL VALVE

Full Port, 1000 psig (69 bar)



| DIMENSIONS (IN) | | | | | | | |
|-----------------|---------|---------|---------|-------------|-----------|-----------|-----------|
| A (Ref) | B (Ref) | C (Ref) | D (NPT) | E (UNC) | F (+.015) | G (+.015) | H (+.015) |
| 1/4" | 2.165 | 4.055 | 1/4" | (2) 3/16-24 | 0.500 | 1.102 | N/A |
| 3/8" | 2.165 | 4.055 | 3/8" | (2) 3/16-24 | 0.500 | 1.102 | N/A |
| 1/2" | 2.559 | 5.236 | 1/2" | (2) 3/16-24 | 0.500 | 1.102 | N/A |
| 3/4" | 2.992 | 5.236 | 3/4" | (2) 3/16-24 | 0.882 | 1.378 | N/A |
| 1" | 3.465 | 6.024 | 1" | (2) 3/16-24 | 0.882 | 1.378 | N/A |
| 1-1/4" | 3.976 | 6.024 | 1-1/4" | (2) 1/4-20 | 1.000 | 1.500 | N/A |
| 1-1/2" | 4.331 | 7.520 | 1-1/2" | (2) 1/4-20 | 1.000 | 1.500 | N/A |
| 2" | 4.882 | 7.520 | 2" | (4) 1/4-20 | 1.000 | 1.500 | 2.000 |
| 2-1/2" | 6.299 | 9.724 | 2-1/2" | (4) 1/4-20 | 1.382 | 2.165 | 2.764 |
| 3" | 6.929 | 9.724 | 3" | (4) 1/4-20 | 1.382 | 2.165 | 2.764 |

The **Series BV2M 2-Piece Stainless Steel Ball Valve** is the economical choice for high quality, SS ball valves for use in chemical, petrochemical, pulp and paper and general applications. The Series BV2M body and endcaps are constructed of investment cast stainless steel, while stem is 316 stainless steel. Seats and body seals are 15% glass reinforced PTFE providing broad media compatibility and bubble tight shutoff to 1000 psig (69 bar). Internally loaded, blowout-proof stem provides safety in the event of overpressure. Full port design allows for maximum Cv with minimal pressure drop. Integral actuator mounting pads allows for ease of automation.

BENEFITS/FEATURES

- Wide chemical compatibility
- Bubble tight shut off to 1000 psig
- Blowout-proof stem
- Actuator mounting pad

APPLICATIONS

- Gas or liquid flow control
- Chemical, petrochemical, pulp and paper, and other general applications

SPECIFICATIONS

End Connections: Female NPT.

Pressure Limits: 1000 psi (69 bar) WOG, 150 psi (10.3 bar) SWP.

Wetted Materials: Body, ball, end cap: CF8M SS; Stem: 316 SS; Seat, thrust washer: RTFE; End gasket, stem packing: PTFE.

Temperature Limits: -20 to 450°F (-29 to 232°C).

Compliance: Meets the technical requirements of EU Directive 2011/65/EU (RoHS II).

MODEL CHART

| Model | Size | Model | Size |
|---------|------|---------|--------|
| BV2M100 | 1/4" | BV2M105 | 1-1/4" |
| BV2M101 | 3/8" | BV2M106 | 1-1/2" |
| BV2M102 | 1/2" | BV2M107 | 2" |
| BV2M103 | 3/4" | BV2M108 | 2-1/2" |
| BV2M104 | 1" | BV2M109 | 3" |