



Deluxe
Milkhouse Heater, 1500W
MODEL HTR80



- Safety tip over switch
- Adjustable thermostat
- Safety overheat protection system
- 2 speed settings
- Carry handle
- Strong metal housing
- Safety brackets



Intertek

Save these Instructions

INTENDED USE:

This product is intended for indoor residential and office use only, not for industrial or other commercial applications. Use only with electrical wiring that is in good working order and that meets applicable codes and ordinances. This heater must be plugged in to a 120V AC, 15 Amp (or larger) circuit. Do not plug anything additional into the same circuit. If you have any questions whether your wiring is adequate, consult a qualified electrician. Risk of fire, overheating, malfunction, property damage, injury or even death may result if not adhered to.

Use the heater only with a working smoke detector located in the vicinity of your heater.

While using your heater, you should follow the **IMPORTANT INSTRUCTIONS** listed below. As part of those instructions, we have used the word "**WARNING**" to indicate the level of hazard: **WARNING** indicates a hazard which, if not avoided, could result in injury or death.

IMPORTANT INSTRUCTIONS

When using electrical appliances, basic safety precautions should always be followed to reduce the risk of fire, electric shock and injury to persons, including the following:

- Read all the instructions before using this heater.
- This heater is hot when in use. To avoid burns, do not let bare skin touch hot surfaces. Use provided handle when moving this heater. Keep combustible materials, such as furniture, pillows, bedding, papers, clothes and curtains at least 3 feet (0.9 meters) from the front of the heater and keep them away from the sides and rear.
- Do not use heater unattended. Use of extreme caution is necessary when any heater is used by or near children, invalids, disabled persons or pets.
- Do not operate the heater with a damaged power cord or after the heater malfunctions, has been dropped or damaged in any manner. Return heater to authorized service facility for examination, electrical or mechanical adjustment or repair.
- Do not use heater outdoors.
- Use your heater only in dry environments. This heater is not intended for use in a bathroom, laundry area, or similar locations, or near sinks, washing machines, swimming pools or other sources of water. Never locate heater where it may fall into a bathtub or other water container. Do not use in damp environments such as flooded basements.
- Do not place the heater on a small, unlevel, uneven or any surface which might allow heater to tip or fall.
- For proper operation, heater should be placed on a smooth, non-combustible, level surface. Do not place on rugs, carpet, vinyl flooring or other plastic surfaces. Not for use outdoors or in wet areas.
- This heater is not designed as a primary heat source.
- Always plug heaters directly into a wall outlet/receptacle. Never use with an extension cord or relocatable power tap (outlet/power strip). Always unplug heater when not in use.
- Do not run power cord under carpeting. Do not cover cord with throw rugs, runners or similar coverings. Arrange cord away from traffic area where it will not be tripped over.
- To disconnect heater, turn controls off then remove plug from outlet.
- Do not insert or allow foreign objects to enter any ventilation or exhaust opening as this may cause an electric shock or fire or damage the heater.
- To prevent a possible fire, do not block air intakes or exhaust in any manner. Do not use on soft surfaces like a bed, where openings may become blocked.
- A heater has hot and arcing or sparking parts inside. Do not use it in areas where gasoline, paint or flammable liquids are used or stored.
- Use this heater only as described in this manual. Any other use not recommended by the manufacturer may cause fire, electric shock or injury to persons or property.

READ & SAVE THESE INSTRUCTIONS

WARNING: SHOCK HAZARD

Use your heater only in dry environments. This heater is not intended for use in a bathroom, laundry area, or similar locations, or near sinks, washing machines, swimming pools or other sources of water. Never locate heater where it may fall into a bathtub or other water receptacle. Do not use in damp environments such as flooded basements.

WARNING: HOT SURFACES

Do not touch body of heater when in use. This heater is hot when in use, to avoid burns, do not let bare skin touch hot surfaces. If provided, use handles when moving this heater.

WARNING: FIRE HAZARD

Heater has hot and arcing or sparking parts inside. Do not use near combustible materials or flammable gases or sources of heat. DO NOT USE in areas where gasoline, paint or flammable materials are used or stored. Keep combustible materials such as furniture, pillows, bedding, papers, clothes and curtains at least 3 feet (0.9 m) from the front of the heater and keep them away from the sides and rear. To prevent a possible fire, do not block air intakes or exhaust in any manner. Do not use on soft surfaces, like a bed, where openings may become blocked. Do not place the heater near a bed because objects such as pillows or blankets can fall off the bed and be ignited by the heater. Do not insert or allow foreign objects to enter any ventilation or exhaust opening as this may cause an electric shock, fire, or damage the heater.

WARNING: ELECTRICAL SHOCK HAZARD

Do not use with damaged cord or plug. Use with adequate electrical system that is up to code.

CAUTION: TO PREVENT ELECTRIC SHOCK

This product has a polarized two prong plug (one blade is wider than the other) that must be fully inserted into a matching properly grounded outlet. This plug is designed to fit a polarized outlet only one way. If the plug does not fit fully into the outlet, reverse the plug. If the plug still does not fit, contact a qualified electrician. Do not attempt to defeat this safety feature.

Do not operate any heater with a damaged cord or plug or after heater malfunctions, has been dropped or damaged in any manner. Do not operate heater with a broken heating element or ceramic cone or any visual imperfections. For repairs covered under warranty, see warranty statement.

PET OWNERS NOTE

The health of birds and some small pets are extremely sensitive to the fumes given off during the initial use of many appliances. Although these fumes are not harmful to humans, it is recommended that this heater not be used around birds and small pets during its initial use until the manufacturing corrosion coatings burn off.

USAGE

HEATER OPERATION: Always operate the heater in the upright position following all instructions and recommendations listed in this manual.


HEATER LOCATION: Before using this heater, ensure that it is placed on a flat, stable surface. The heater should not be placed immediately under a power outlet.

HEATER CONNECTION: Plug heater directly into 120 Volts AC, 60Hz wall outlet. Be sure plug fits tightly in outlet. A loose connection may cause overheating and damage to the plug or heater.

NOTE: To prevent overloading a circuit, do not plug the heater into a circuit that is servicing other electrical needs.

ASSEMBLY INSTRUCTIONS

Before initial use some assembly is required. With a phillips screwdriver, attach metal handle to heater body using screws provided as shown in the photo.




TURNING HEATER ON

1. To start the heater, turn the On/Off Power Level/Fan Dial from the OFF position to the 1,300 or 1,500 Watt setting.
2. Rotate the Thermostat Control clockwise to the HIGH THERMOSTAT position as described further.

NOTE: During the heaters initial use, you may experience a slight odor or smoking. This is the result of the heating element lubrication “burning off”. This is normal and will go away after a few minutes of use.

POWER INDICATOR LIGHT:

This heater is equipped with a Power Indicator Light. The power light will illuminate when the unit is turned on.



POWER LEVEL SWITCH:

This heater has two heat settings: 1,300 and 1,500 Watts. Use the higher setting (1,500 Watt) to raise the room temperature quickly. When the desired temperature is reached, use the lower 1,300 Watt setting. It is usually sufficient to maintain a comfortable temperature.

ADJUSTABLE THERMOSTAT WITH ANTI-FREEZE SETTING:

After heater has been turned on and the room has reached the desired temperature, slowly rotate the thermostat knob counter-clockwise until the heater shuts off (you should hear a faint “click”). By leaving the thermostat at this setting, it will automatically maintain this temperature. To lower temperature, rotate the knob further counter-clockwise (towards the LOW position). To raise the temperature, rotate the thermostat knob clockwise (towards the HIGH position).

When set to the ANTI-FREEZE mode, the heater will turn on whenever the temperature drops below 40°F, which is helpful to economically prevent ice formation in garages and other unheated spaces.

TURNING HEATER OFF:

Turn the On/Off Power Level/Fan Dial to the OFF position before unplugging or plugging in the heater. Heater should be unplugged when not in use. Turn both dial controls to OFF, then remove plug from outlet.

IMPORTANT SAFETY FEATURES

The power indicator light, located near the control panel, lights whenever the heater is turned on.

The heater is equipped with an automatic overheat protection device located inside the body of the heater. If the heater grille is obstructed, or if the heater gets too hot for any reason, the automatic overheat protection device will turn the heater off. To reset the heater, simply turn power off and unplug the heater for 10 minutes until it cools down and then you may plug the heater in and restart. Be sure that the heater is on a smooth level surface with no obstructions.

The heater is also equipped with a safety tip-over switch to turn power off to the heater when the heater tips over. To resume heater functions simply stand heater upright.

CARE AND MAINTENANCE

WARNING: ALWAYS UNPLUG THE CORD BEFORE MOVING OR SERVICING. Do not use harsh chemical or abrasive cleaners. DO NOT IMMERSE THE HEATER IN WATER. Allow heater to dry completely before use.

CLEANING: IMPORTANT! DO NOT IMMERSE HEATER IN WATER! Clean the heater grille with the vacuum brush attachment on your vacuum cleaner. This will remove lint and dirt from inside the heater. DO NOT ATTEMPT TO TAKE APART THE HEATER. DO NOT REMOVE THE HEATER GRILLE. Clean the body of the heater with a soft cloth.

CAUTION: Do not use gasoline, benzene, paint thinner, harsh cleaners, etc. as they will damage the heater. NEVER USE ALCOHOL OR SOLVENTS.

REPAIR: DO NOT OPERATE THE HEATER WITHOUT THE GRILLE IN PLACE. DO NOT USE THE HEATER IF IT HAS MALFUNCTIONED OR BECOME DAMAGED IN ANY WAY.

STORAGE: Keep original carton for storage of the heater. Coil and tie the power cord to avoid damage during storage.

LIMITED WARRANTY

A limited warranty is extended to the original purchaser of this heater and Proaira warrants against malfunction due to defects in material or workmanship for a period of one (1) year from the original date of purchase (the "Warranty Period"). If such a defect is discovered within the Warranty Period, Proaira will, at its option, repair or replace the product at no cost after a thorough review of the defect. Replacements outside of the Warranty Period will require a fee to cover materials, labor, handling and shipping.

This limited warranty does not apply to defects resulting from misuse or use contrary to the owner's manual and safety guidelines, damage caused by an improper voltage, damage caused by use outdoors, modification, alteration, repair or service of the product by a third party, mishandling, improper maintenance, commercial use of the product, damages which occur in shipment or are attributed to acts of God.

This limited warranty does not imply or assume any responsibility for consequential damages that may result from the use, misuse, or the lack of routine maintenance of this heating appliance. This limited warranty does not cover claims which do not involve defective material or workmanship. FAILURE TO PERFORM GENERAL MAINTENANCE WILL VOID THIS LIMITED WARRANTY.

THIS LIMITED WARRANTY IS GIVEN TO THE ORIGINAL PURCHASER IN LIEU OF ALL OTHER WARRANTIES, EXPRESS OR IMPLIED, INCLUDING BUT NOT LIMITED TO THE WARRANTIES OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PRODUCT. THE REMEDY PROVIDED IN THIS LIMITED WARRANTY IS EXCLUSIVE AND IS GRANTED IN LIEU OF ALL OTHER REMEDIES. IN NO EVENT WILL PROAIRA BE LIABLE FOR INCIDENTAL OR CONSEQUENTIAL DAMAGES.

Some states do not allow the exclusion or limitation of incidental or consequential damages or allow limitations on how long an implied warranty lasts, so the above limitations or exclusions may not apply to you. This limited warranty gives you specific legal rights, and you may have other rights that vary from state to state.

For full details, please contact Proaira Customer Service with proof of purchase.

Customer Service:

Phone: (877) 599-4747

Fax: (877) 600-4747

Email: info@proaira.com

Manufactured for:

Proaira

1060 Commerce Ave.

Union, NJ 07083 USA

(877) 599-4747

www.proaira.com