

DCP-L5650DN

Copy • Print • Scan

Business Laser Multi-Function Copier with Advanced Duplex and Networking



Top Features:

Fast, High-Quality Printing & Copying

- Help increase your productivity with a black print and copy speed of up to 42ppm

3.7" Color Touchscreen Display

- Easy menu navigation and creation of up to 48 customized shortcuts via 3.7" color Touchscreen display. Plus, scan to popular cloud services^Δ including DROPBOX, GOOGLE DRIVE[™], ONENOTE[®] and more

Fast, Duplex Scanning

- 70-page capacity duplex auto document feeder scans both sides of the page in a single-pass for two-sided scanning up to 56ipm (mono)^Δ

Flexible Paper Handling

- 250-sheet capacity paper tray adjustable for letter or legal plus a 50-sheet capacity multi-purpose tray for envelopes or alternative media types. Total capacity expandable to 1,340 sheets with optional add-on trays.*

Built-In Networking

- Easily share with others via built-in Gigabit Ethernet networking or print locally via USB interface

Cost-Efficient Output

- Help reduce running costs due to a high-yield 8,000-page[▽] replacement toner cartridge

Print from/Scan to Your Mobile Device[□]

- Print from your mobile device via: AirPrint[™], Google Cloud Print[™] 2.0, Mopria[®], Brother iPrint&Scan, Cortado Workplace

Legal-Size Document Glass

- Copy or color scan bound materials or up to legal-size documents

Advanced Security Features

- Active Directory for network user authentication to help protect against unauthorized access to device. Other security features include Secure Function Lock, LDAP, SSL/TLS, and more.

Outstanding Customer Support

- 1-year limited warranty with free phone support for the life of your machine



* Additional purchase required

[□] Requires connection to a wireless network. See www.connectprintshare.com for details, availability, and mobile device compatibility

All trademarks and registered trademarks referenced herein are the property of their respective companies. Windows, Windows Vista, Windows Server, SharePoint, OneDrive, OneNote, and the Windows logo are trademarks of Microsoft Corporation in the United States and/or other countries. Mac OS, the Mac logo and OS X are trademarks of Apple Inc. registered in the U.S. and other countries. AirPrint and the AirPrint logo are trademarks of Apple Inc. ©2015 Google Inc. All rights reserved. Google Drive, Google Cloud Print, and Picasa are trademarks of Google Inc. The Mopria logo is a trademark of Mopria Alliance, Inc. Cortado is a trademark of Cortado AG. EVERNOTE is a trademark of Evernote Corporation and used under a license. FLICKR is a registered trademark of Yahoo! Inc. All specifications are subject to change without notice. Images are for illustrative purposes only.

[▽] Approximate toner cartridge yield in accordance with ISO/IEC 19752 (letter/A4)

^Δ Requires an Internet connection and an account with desired service. See www.connectprintshare.com for details.

^Δ Scan speed measured with all advanced features turned off using LTR size test documents at 200dpi.

Specifications:

Print Technology	Electrophotographic Laser
LCD Display (type/size)	3.7" Color Touchscreen
Paper Size (maximum)	Up to 8.5" x 14" (legal)
Print Speed (maximum)	Up to 42ppm
Print Resolution (maximum)	Up to 1200 x 1200 dpi
Emulations	PCL6, BR-Script3*, IBM Proprinter, Epson FX, PDF version 1.7, XPS Version 1.0
Memory (std. / max.)	512MB / 512MB
Automatic Duplex	Print, plus single-pass copy/scan
Paper Input Capacity (maximum)^{oo}	250-sheet capacity paper tray, 50-sheet capacity multi-purpose tray
Optional Input Capacity (max. *)^{oo}	1,340 sheets via optional trays
Output Capacity (maximum)^{oo}	150 sheets (face down), 1 sheet (face up)
Auto Document Feeder^{oo}	Up to 70 pages
Standard Interfaces	Gigabit Ethernet, Hi-Speed USB 2.0
USB Host	Yes, front
Copy Speed / Copy Resolution (maximum)	Up to 42cpm / Up to 1200 x 600 dpi
Copy Options	Sorting, N-in-1, Multi-copying (up to 99), ID Copy, Reduce/Enlarge 25 - 400% in 1% increments
Scan Speed (maximum) [▲]	Simplex: Up to 28ipm (black) / 20ipm (color) Duplex: Up to 56ipm (black) / 34ipm (color)
Document Glass Size	8.5" x 14" (legal)
Scan Resolution (maximum)	Optical: Up to 1200 x 1200 dpi (from document glass) Interpolated: Up to 19200 x 19200 dpi
Scan To Capability	File, Image, E-mail, OCR, File, FTP, SSH Server (SFTP), USB [▲] , SharePoint [®] , Cloud [▲] (Web Connect), E-mail Server ¹ , Network Folder ^{**} (CIFS), Easy Scan to E-mail
Web Connect[▲]	GOOGLE DRIVE [™] , EVERNOTE [®] , ONEDRIVE [®] , ONENOTE [®] , DROPBOX, BOX, FACEBOOK [™] , FLICKR [®] , PICASA Web Albums [™]
Operating Systems Compatibility^o	Windows [®] : XP Home / XP Professional / XP Professional x64 Edition / Windows Vista [®] / Windows [®] 7, 8, 8.1, 10 / Windows Server [®] 2003 / 2003 R2 (32/64 bit) / 2008 / 2008 R2 / 2012 / 2012 R2 Mac [®] OS X [®] v10.8.5, 10.9.x, 10.10.x Linux
Mobile Device Compatibility^o	AirPrint [™] , Google Cloud Print [™] 2.0, Brother iPrint&Scan Cortado Workplace, Mopria [®]
Security Features	Secure Function Lock, Active Directory, Enterprise Security (802.1x), Slot Lock, Secure Print, SSL/TLS, IPsec
Maximum Monthly Duty Cycle^o	Up to 50,000 pages/month
Recommended Monthly Volume[*]	Up to 3,500 pages/month
Warranty	1-year limited warranty

Supplies & Accessories*:

TN-820	Standard Yield Toner Cartridge (approx. 3,000 pages) [▼]
TN-850	High-Yield Toner Cartridge (approx. 8,000 pages) [▼]
DR-820	Drum Unit (approx. 30,000 pages) [^]
LT-5500	Optional 250-Sheet Capacity Paper Tray
LT-6500	Optional 520-Sheet Capacity Paper Tray
BP60MPLTR	Multi-Purpose Paper (Letter, 500 sheets)

Setup Information:

UPC Code	012502641971
Unit Dimensions	19.5" W x 16.8" D x 19.1" H
Unit Weight	37.6 lbs.
Carton Dimensions	23.6" W x 20.7" D x 24.8" H
Carton Weight	45.5 lbs.
Pallet Quantity	4
Pallet Tiers	1
Pallet Quantity per Tier	4
Pallet Size	48" x 40"
Pallet + Cartons Height	29.8"
Pallet + Carton Weight	232.0 lbs.
Country of Origin	Vietnam
Tarrif / Harmonized Code	8443.31.0000

Carton Contents:

Brother DCP-L5650DN
Standard Yield Toner Cartridge (3,000 pages) [▼]
DR-820 Drum Unit (30,000 pages [^])
Quick Setup and Basic User's Guide
Installation CD-ROM
AC Power Cord

Scannable Barcode:



Working with you for a better environment

At Brother, our green initiative is simple. We strive to take responsibility, act respectfully and try to make a positive difference to help build a society where sustainable development can be achieved. We call this approach Brother Earth. www.brotherearth.com



* PostScript[®]3[™] compatible.
^{*} Additional purchase required.
^{oo} Maximum capacity based on using 20 lb. paper.
[▲] PDF (up to ver. 1.7), JPEG, XPS and Secure PDF files (scan only)
¹ Requires SMTP/POP3 mail server support. Download from <http://solutions.brother.com>
^{**} Windows only.
^o Server 2003/2008/2012 network printing only.
[▲] Requires an Internet connection and an account with desired service. See www.connectprintshare.com for details.
^o Requires connection to a wireless network. See www.connectprintshare.com for details, availability and mobile device compatibility.
^{*} The recommended range of monthly printed pages to achieve the best possible performance and printer life. Printers are intended to handle occasional usage beyond this range with little or no effect. Consistently printing above the

recommended print volume, however, may adversely affect the print quality or life of the machine. It is always best to choose a printer with an appropriate recommended print volume to allow for any anticipated increase in printing needs.
^o Maximum number of printed pages per month can be used to compare designed durability between like Brother products.
[▼] For maximum printer life, it is best to choose a printer with a duty cycle that far exceeds your print requirements.
[^] Approximate toner cartridge yield in accordance with ISO/IEC 19752 (letter/A4).
[▲] Approximately 30,000 pages based on 1 page per job and 50,000 pages based on 3 pages per job [letter/A4 simplex pages]. The number of pages may be affected due to a variety of factors including but not limited to media type and media size.
[▲] Scan speed measured with all advanced features turned off using LTR size test documents at 200dpi.