

## Compact Black & White Laser All-in-One

MFC-L2710DW



**The Brother MFC-L2710DW All-in-One is a great choice for home or small offices that need full functionality in a compact footprint.**

- Up to 50-sheet automatic document feeder helps save time with multi-page copy, scan & fax
- Print wirelessly from your desktop, laptop, smartphone and tablet<sup>□</sup>
- Helps save paper with automatic duplex (2-sided) printing
- The 250-sheet paper capacity offers less refills and handles up to legal sized paper
- Engineered for increased efficiency with fast print speeds of up to 32 ppm
- Share with multiple users via built-in wireless and Ethernet, or connect locally to a single computer via USB

# MFC-L2710DW

## Specifications:

Print Technology	Electrophotographic Laser
LCD Display (type/size)	2-line Mono
Paper Size (maximum)	Paper Tray: Up to 8.5" x 14" (legal) Manual Feed Slot: 3" to 8.5" (W), 5" to 14" (L)
Print Speed (maximum)	Up to 32ppm
Print Resolution (maximum)	Up to 2400 x 600 dpi
Emulations	GDI
Memory (standard / maximum)	64MB / 64MB
Duplex Printing Capability	Yes
Paper Input Capacity (maximum) <sup>∞</sup>	250-sheet capacity lower paper tray, plus a single-sheet manual feed slot
Output Capacity (maximum) <sup>∞</sup>	100 sheets (face down), 1 sheet (face up)
Auto Document Feeder <sup>∞</sup>	Up to 50-pages
Standard Interfaces	Wireless 802.11b/g/n, Ethernet, Hi-Speed USB 2.0
Copy Speed (maximum)	Up to 32cpm
Copy Resolution (maximum)	600 x 600 dpi
Copy Reduction/Enlargement	25% - 400% in 1% increments
Copy Options	Sorting, N-in-1, Multi-copying/stack (up to 99), ID copy
Scanner Type	Color Flatbed with ADF
Document Glass Size	8.5" x 11" (letter)
Scan Resolution (maximum)	<b>Optical:</b> Up to 1200 x 1200 dpi <sup>3</sup> <b>Interpolated:</b> Up to 19200 x 19200 dpi
Scan To Capability	File, Image, E-mail, OCR, Microsoft® SharePoint®*
Document Viewer / OCR Software	Nuance™ PaperPort™ 14SE w/ OCR for Windows® (by download)
Fax Modem	33.6K bps
Fax Page Memory (maximum)	Up to 400 pages <sup>1</sup>
Speed Dial Locations	200
PC Fax Capability <sup>2</sup>	Yes
Operating Systems Compatibility <sup>∞</sup>	Windows® 8.1, 8, 7 / Windows® 10 Home / 10 Pro / 10 Education / 10 Enterprise Windows Server® 2016 / 2012 R2 / 2012 / 2008 R2 / 2008 Mac® OS X® v10.10.5, 10.11.x, 10.12.x, 10.13.x Linux
Mobile Device Compatibility <sup>∞</sup>	AirPrint®, Google Cloud Print™, Brother iPrint&Scan, Wi-Fi Direct®
Maximum Monthly Duty Cycle <sup>∞</sup>	Up to 15,000 pages/month
Recommended Monthly Volume <sup>∞</sup>	Up to 2,000 pages/month
Warranty	1-year limited warranty

## Supplies & Accessories\*:

TN-730	Standard Yield Toner (approx. 1,200 pages)▼
TN-760	High-Yield Toner (approx. 3,000 pages)▼
DR-730	Drum Unit (approx. 12,000 pages)▲
BP60MPLTR	Letter-size Multi Purpose Paper (500 sheets)



At your side support. Online, call or live chat – Brother provides FREE technical support for the life of your product. At Brother, we want to ensure that your experience with us is exceptional. Visit us at [brother-usa.com](http://brother-usa.com) where you can download the latest product drivers and software, view product manuals, learn how to get the most out of your product with how-to videos and find answers to frequently asked questions.



### Working with you for a better environment

At Brother, our green initiative is simple. We strive to take responsibility, act respectfully and try to make a positive difference to help build a society where sustainable development can be achieved. We call this approach Brother Earth. [www.brotherearth.com](http://www.brotherearth.com)

COMPATIBLE WITH  
**WINDOWS**



▲ From ready mode and standard tray  
\* Additional purchase required.

∞ Maximum capacity based on using 20 lb. paper.

<sup>1</sup> Some advanced features are not supported under all operating systems or drivers. Refer to User's Guide at [www.brother.com](http://www.brother.com)

<sup>2</sup> PC Fax Receive not available for Mac users. B&W only.

<sup>3</sup> Max. dpi from glass; max 600 x 600 dpi from ADF.

∞ Requires connection to a wireless network. See [www.brother.com](http://www.brother.com) for details, availability and mobile device compatibility.

∞ Maximum number of printed pages per month can be used to compare designed durability between like Brother products. For maximum printer life, it is best to choose a printer with a duty cycle that far exceeds your print requirements.

\* The recommended range of monthly printed pages to achieve the best possible performance and printer life. Printers are intended to handle occasional usage beyond this range with little or no effect. Consistently printing above the recommended print volume, however, may adversely affect the print quality or life of the machine. It is always best to choose a printer with an appropriate recommended print volume to allow for any anticipated increase in printing needs.

▼ Approximate toner cartridge yield in accordance with ISO/IEC 19752 (letter/A4).

▲ Drum yield is approx., and may vary by type of use.