

Specifications:

Print Technology	Digital Color LED
LCD Display (type/size)	3.7" Color Touchscreen
Paper Size (maximum)	Up to 8.5" x 14" (legal)
Print Speed (maximum)	Black: up to 25ppm Color: up to 25ppm
Print Resolution (maximum)	Up to 600 x 2400 dpi
Automatic Duplex Printing	Yes
Emulations	PCL®6, GDI, BR-Script3*
Memory (std. / max.)	512MB / 512MB
Auto Document Feeder^o	Up to 50 pages
Standard Interfaces	Wireless 802.11b/g/n, Ethernet, Hi-Speed USB 2.0
USB Direct Interface	Yes
Copy Speed (maximum)	Black: up to 25cpm Color: up to 25cpm
Copy Resolution (maximum)	600 x 600 dpi
Copy Reduction/Enlargement	25% - 400% in 1% increments
Copy Options	Sorting, N-in-1, Multi-copying (up to 99), ID copy
Scanner Type	Color Flatbed with ADF
Document Glass Size	8.5" x 11.7"
Scan Resolution	Optical: 1200 x 2400 dpi (from document glass) Interpolated: 19200 x 19200 dpi
Scan to Capability	E-mail, Image, OCR, File, USB, FTP, Network [†]
Fax Modem	33.6k bps
Fax Page Memory (maximum)¹	Up to 500 pages
Speed Dial Locations	200
PC Fax Compatibility²	Yes
Operating Systems Compatibility^o	Windows 7, 8, 8.1, 10 / Server 2008, Server 2008 R2, Server 2012, Server 2012 R2, Server 2016 Mac®v10.11.6, 10.12.x, 10.13.x (Download only)
Web Connect[†]	DROPBOX, GOOGLE DRIVE™, EVERNOTE®, ONEDRIVE, ONENOTE, BOX
Brother Cloud Apps³	Office Print, Easy Scan to E-mail, Scan to mobile
Mobile Device Compatibility^o	AirPrint®, Google Cloud Print™, Brother iPrint&Scan (free downloadable app), Mopria, and Wi-Fi Direct®
Maximum Monthly Duty Cycle^o	Up to 30,000 pages
Recommended Monthly Volume^o	Up to 1,500 pages
Warranty	1-year Limited Warranty
ENERGY STAR® Qualified	Yes

* PostScript®3™compatible.

† Windows Only.

^o Maximum capacity based on using 20 lb. paper.

^o Additional purchase required.

^o Maximum number of printed pages per month can be used to compare designed durability between like Brother products. For maximum printer life, it is best to choose a printer with a duty cycle that far exceeds your print requirements.

^o Requires connection to a wireless network.

^o Server 2003/2008/2008R2 Printing only

^o Requires an internet connection and account with desired service.

^o The recommended range of monthly printed pages to achieve the best possible performance and printer life. Printers are intended to handle occasional usage beyond this range with little or no effect. Consistently printing above the recommended print volume, however, may adversely affect the print quality or life of the machine. It is always best to choose a printer with an appropriate recommended print volume to allow for any anticipated increase in printing needs.

[^] Approximate yield in accordance with ISO/IEC 19798 (Letter/A4).

^{**} Drum yield is approximate and may vary based on type of use.


^{^^} Approximate yield based on A4 or Letter size single-sided pages.

¹ Using Brother No. 1 Chart with JBIG coding and standard resolution.

² B&W only. PC Fax Send only for Mac users.

³ Requires an Internet connection.

Supplies*:



TN223BK	Standard Yield Black Toner Cartridge (1,400 pgs) [^]
TN223C	Standard Yield Cyan Toner Cartridge (1,300 pgs) [^]
TN223M	Standard Yield Magenta Toner Cartridge (1,300 pgs) [^]
TN223Y	Standard Yield Yellow Toner Cartridge (1,300 pgs) [^]
TN227BK	High Yield Black Toner Cartridge (3,000 pgs) [^]
TN227C	High Yield Cyan Toner Cartridge (2,300 pgs) [^]
TN227M	High Yield Magenta Toner Cartridge (2,300 pgs) [^]
TN227Y	High Yield Yellow Toner Cartridge (2,300 pgs) [^]
DR223CL	Drum Unit Set (18,000 pgs) ^{**}
BU223CL	Belt Unit (50,000 pgs A4/Letter)
WT223CL	Waste Toner Box (50,000 pgs) ^{**}
BP60MPLTR	Multi Purpose Paper (Letter, 500 sheets)

Setup Information:

UPC Code	012502651796
Unit Dimensions	16.1" W x 18.7" D x 16.3" H
Unit Weight	51.5 lbs.
Carton Dimensions	23.2" W x 20.6" D x 22.4" H
Carton Weight	60.7 lbs.
Pallet Quantity	8
Pallet Tiers	2
Pallet Quantity per Tier	4
Pallet Size	48" x 40"
Pallet + Cartons Height	49.7"
Pallet + Carton Weight	515.9 lbs.
Country of Origin	China
Tariff / Harmonized Code	8443.31.0000

Carton Contents:

MFC-L3750CDW Digital Color Multi-Function Center
Starter Black Toner Cartridge (1,000 pages) [^]
Starter Cyan Toner Cartridge (1,000 pages) [^]
Starter Yellow Toner Cartridge (1,000 pages) [^]
Starter Magenta Toner Cartridge (1,000 pages) [^]
DR223CL Drum Unit Set (18,000 pgs) ^{**}
CD-ROM All Drivers/Software
Quick Set-Up Guide and User's Guide

Scannable Barcode:



Working with you for a better environment

At Brother, our green initiative is simple. We strive to take responsibility, act respectfully and try to make a positive difference to help build a society where sustainable development can be achieved. We call this approach Brother Earth. www.brotherearth.com

