



THE PERFECT EVERYDAY ALL-IN-ONE PRINTER

What kind of printer do you need to help you do what you do every day? Probably a printer that does it all with a reasonably sized design, right? The PIXMA TS9520 may be the perfect everyday printer for you. Of course it's wireless¹, supports AirPrint^{®2} and Mopria[®] Print Service³, and can print crisp documents, all the way up to 11"x17". It can also print beautiful photos and even has a built-in SD Memory Card slot⁴. There is an ADF on top for copying stacks of paper, it supports 2-sided printing, and has a 4.3" Touch LCD on the front to control it all.

CORE FEATURES

<p>AirPrint</p>	<p>5 Individual Inks</p>	<p>11" x 17"</p>	<p>ADF</p>
<p>Quickly print directly from your iPad or iPhone with AIRPRINT^{®2}.</p>	<p>With a FIVE INDIVIDUAL INK SYSTEM, only replace the ink that runs out!</p>	<p>You can print large documents up to 11" x 17" such as calendars, schedules, posters and more!</p>	<p>Easily scan and copy multiple page documents with the built-in AUTO DOCUMENT FEEDER.</p>
<p>4.3" LCD Touch</p>	<p>Memory Card</p>	<p>mopria[®]</p>	<p>Wi-Fi[®] CERTIFIED</p>
<p>Intuitive control with an effortless USER INTERFACE & 4.3" LCD TOUCHSCREEN.</p>	<p>Enjoy easy photo printing with a built-in SD MEMORY CARD READER.⁴</p>	<p>With the MOPRIA[®] PRINT SERVICE easily print right from your Android phone or tablet!³</p>	<p>Print from any room in the house with seamless Wi-Fi^{®1}!</p>

EFFICIENT EVERYDAY PRINTING

The PIXMA TS9520 has a 5-Color Individual Ink System, that means it's ready for lots of detailed documents with sharp black text and great looking photos. It can even support various paper types & sizes, from 3.5"x3.5" up to 11"x17".

ENHANCED CONNECTIVITY

You can print from all your favorite devices, whether that is a smartphone, tablet or computer. With AirPrint^{®2}, Mopria[®] Print Service³, Wi-Fi^{®1}, and Ethernet - the PIXMA TS9520 has you covered.

VERSATILE PRINTING, COPYING & SCANNING

With features like 11"x17" paper support, booklet layout copy, oversized scanning and an ADF (Auto Document Feeder) for scanning multi-page documents, the PIXMA TS9520 is extremely versatile and ready to handle lots of different needs.

CONVENIENCE BUILT-IN

With features like Auto Power On/Off, a built-in ADF, Wireless Connect⁵ and Wi-Fi^{®1} - it's easy to see why PIXMA printers are so simple to use.

TECHNICAL SPECIFICATIONS

PRINT

Print Features	AirPrint ² , Auto 2-Sided (Duplex) Printing, Auto Photo Fix, Black Ink / Color Ink Only Printing, Bluetooth Printing ⁶ , Borderless Printing ⁷ , Business Card Printing, Canon PRINT app ⁸ , Disc Label Printing, Document Printing, Easy-PhotoPrint Editor Software/app ⁹ , Google Cloud Print ¹⁰ , Greeting Cards, Label Printing, Memory Card Printing ⁴ , Message In Print ¹¹ , Mopria Print Service ³ , Pattern Paper Printing, Photo Printing, PIXMA Cloud Link ¹² , Square Media Printing, Template Printing, Wireless PictBridge ¹³ , Wireless Printing ¹
Print Speed¹⁴	4" x 6" Photo: Approx. 21 Seconds (Borderless) ESAT (Black): Approx. 15.0 ipm ESAT (Color): Approx. 10.0 ipm
Number of Nozzles	Color: 3,072 / Pigment Black: 1,024 / Total: 4,096
Print Resolution¹⁵	Up to 4800 x 1200 dpi
Paper Sizes	3.5" x 3.5", 4" x 4", 4" x 6", 5" x 5", 5" x 7", 8" x 10", Letter, 11" x 17", 12" x 12", Legal, U.S. #10 Envelopes
Media Compatibility	Plain: Plain Paper, Canon High Resolution Paper; Super High Gloss: Photo Paper Pro Platinum; Glossy: Photo Paper Plus Glossy II, Photo Paper Glossy; Semi-Gloss: Photo Paper Plus Semi-Gloss, Photo Paper Pro Luster; Matte: Matte Photo Paper Other: Greeting Cards, Printable CD/DVD/Blu-ray Discs, T-Shirt Transfers, U.S. #10 Envelopes
Paper Capacity	Rear Paper Tray: 100 Sheets of Plain Paper OR Photo Paper: 20 Sheets of 4" x 6" / 10 Sheets of 5" x 7" Front Paper Cassette: 100 Sheets of Plain Paper
Memory Card Support⁴	SD TM , SDHC TM , SDXC TM , miniSD TM , miniSDHC TM , microSD TM , microSDHC TM , microSDXC TM

COPY

Copy Features	4-on-1 / 2-on-1 Copy, Auto Document Feeder (ADF), Auto Exposure Copy, Booklet Layout Copy, Borderless Copy, Collated Copy (ADF Only), Disc Label Copy, Document Removal Reminder, Fit-to-Page, Frame Erase Copy, ID Card Copy, Large (Oversized) Document Copy, Manual 2-Sided Copy With ADF, Multiple Copy (Up To 99 Pages), Photo Fade Restoration, Preset Copy Ratios, Reduction/Enlargement (25% - 400%), Standard Copy, Two-Sided Copy
Copy Speed¹⁴	FCOT (Color): Approx. 19 Seconds

SCAN

Scan Features	Auto Document Feeder (ADF), Auto Scan Mode ¹⁶ , Attach to Email, Document Removal Reminder, Multi-Page PDF, Save to PC, Scan to Canon PRINT app ⁸ , Wireless Scanning ¹
Scanner Type	Contact Image Sensor (CIS)
Scanning Method	Flatbed & ADF (Auto Document Feeder)
Scanning Resolution¹⁷	Flatbed: 1200 x 2400 dpi (Optical) ADF: 600 x 600 dpi (Optical)
Maximum Color Scanning Bit Depth	16-bit Internal (Per RGB Channel) 8-bit External (Per RGB Channel)
Maximum Document Size	Flatbed: 8.5" x 11.7" (Letter/A4) ADF: 8.5" x 14.0" (Legal)
ADF Capacity	20 Sheets of Plain Paper / 5 Sheets of Legal Size Paper

FAX

Fax Capable	No
--------------------	----

INK INFORMATION

Ink Type	PGI-280 Pigment Black Ink CLI-281 Dye Based Ink
Ink Tank & Fill Volume	PGI-280 PGBK: 11.2 ml (Std.) 18.5 ml (XL) 25.7 ml (XXL) CLI-281 BK, C, M, Y: 5.6 ml (Std.) 8.3 ml (XL) 11.7 ml (XXL)
Print Longevity	The ChromaLife100 System¹⁸ protects your photos from fading up to: <ul style="list-style-type: none"> • 100 Years Album Life, or • 30 Years Behind Glass (Light Fastness), or • 20 Years Without The Glass (Gas Fastness)

GENERAL

CONNECTIVITY

Hi-Speed USB
Ethernet
PictBridge (LAN/Wireless LAN)¹³
Wi-Fi* (802.11b/g/n wireless networking, 2.4 GHz)¹
Memory Card Slot⁴
Bluetooth 4.0 LE (Low Energy)⁶

DISPLAY

4.3" LCD Touchscreen

GENERAL FEATURES

5-Color Individual Ink System, Auto Power On/Off, Auto Print Head Alignment, Bluetooth⁶, Canon PRINT app⁸, CREATIVE PARK PREMIUM¹⁹, Document Removal Reminder, Energy Star[®] Certified, Hybrid Ink System, PIXMA Cloud Link¹², Quiet Mode, Wireless Connect⁵

SMART ASSISTANT & AUTOMATION SUPPORT

Amazon AlexaTM (Native Support)²⁰
Google AssistantTM (Using IFTTT)²¹
IFTTT (IF This Then That) Support²¹

OS COMPATIBILITY

Windows:²² Windows[®] 10, Windows 8.1, Windows 7 SP1
Mac:²³ Mac OS[®] X v10.10.5 - macOS v10.13 (High Sierra)
Mobile Operating Systems:²⁴ iOS[®], Android, Windows 10 Mobile, and Fire OS (Amazon Fire) devices²⁵

MOBILE APPS (iOS[®] / ANDROIDTM)

Canon PRINT app⁸
Easy-PhotoPrint Editor app⁹
Message In Print app¹¹

SOFTWARE (WINDOWS²²/MAC²³)

PIXMA TS9520 Wireless Inkjet All-In-One Printer Driver
Scan Utility (Win/Mac) / Scan Utility Lite (Mac Only)
Easy-PhotoPrint Editor Software⁹
PosterArtist Lite²⁶
Master Setup
My Printer (Windows Only)
Network Tool
Quick Menu











WARRANTY²⁷

1-Year Limited Warranty with InstantExchange Program. 1-Year toll-free 100% U.S.-based technical phone support.







BOX CONTENTS

PIXMA TS9520 Wireless Inkjet All-In-One Printer
Multi-Purpose Tray
4"x6" Photo Paper Sample Pack (3 Sheets of PP-301)
Setup CD
Set of Standard Ink Tanks
Power Cord

ORDERING INFORMATION

MODEL NUMBER	DESCRIPTION	ITEM NUMBER	UPC CODE
 PIXMA TS9520 *	Wireless Inkjet All-In-One Printer	2988C002[AA]	 0 13803 30575 3
COMPATIBLE INK	DESCRIPTION	ITEM NUMBER	UPC CODE
 PGI-280 PGBK XXL*	XXL Pigment Black Ink Tank	1967C001[AA]	 0 13803 28726 4
 CLI-281 BK XXL*	XXL Black Ink Tank	1983C001[AA]	 0 13803 28733 2
 CLI-281 C XXL*	XXL Cyan Ink Tank	1980C001[AA]	 0 13803 28730 1
 CLI-281 M XXL*	XXL Magenta Ink Tank	1981C001[AA]	 0 13803 28736 3
 CLI-281 Y XXL*	XXL Yellow Ink Tank	1982C001[AA]	 0 13803 28743 1
 PGI-280 PGBK XL*	XL Pigment Black Ink Tank	2021C001[AA]	 0 13803 28749 3
 CLI-281 BK XL*	XL Black Ink Tank	2037C001[AA]	 0 13803 28755 4
 CLI-281 C XL*	XL Cyan Ink Tank	2034C001[AA]	 0 13803 28760 8
 CLI-281 M XL*	XL Magenta Ink Tank	2035C001[AA]	 0 13803 28765 3
 CLI-281 Y XL*	XL Yellow Ink Tank	2036C001[AA]	 0 13803 28774 5
 PGI-280 PGBK*	Pigment Black Ink Tank	2075C001[AA]	 0 13803 28779 0
 CLI-281 BK*	Black Ink Tank	2091C001[AA]	 0 13803 28785 1
 CLI-281 C*	Cyan Ink Tank	2088C001[AA]	 0 13803 28787 5
 CLI-281 M*	Magenta Ink Tank	2089C001[AA]	 0 13803 28789 9
 CLI-281 Y*	Yellow Ink Tank	2090C001[AA]	 0 13803 28795 0

ORDERING INFORMATION CONT.

COMPATIBLE INK PACKS	DESCRIPTION	ITEM NUMBER	UPC CODE
 PGI-280 XL / CLI-281 / PP-301 Combo*	PGI-280XL PGBK / CLI-281 CMY / 50 Sheets PP-301 Combo Pack	2021C006[AA]	 6 60685 17425 2
 CLI-281 XL BKCMY 4 Pack*	CLI-281 XL BKCMY 4 Color Value Pack	2037C005[AA]	 6 60685 17427 6
 CLI-281 BKCMY 4 Pack*	CLI-281 BKCMY 4 Color Value Pack	2091C005[AA]	 6 60685 17426 9

* TSCA INFORMATION

TSCA Sec. 4,5,6,7,8,12b

This product contains substances which are subject to TSCA Section 5(e) Consent Order. Do not use this product other than as inkjet printer ink. Do not release this product into the waters of the United States. This product is subject to TSCA Section 12(b) export notification requirements. If you need more information about the TSCA Section 12(b), please contact Canon U.S.A., Inc.


ORIGIN	
Country of Origin	Thailand
Tariff Number	8443310000
PRINTER INFORMATION	
Printer Dimensions (Closed)	18.5" (L) x 14.5" (W) x 7.6" (H)
Printer Dimensions (Paper Installed)	18.5" (L) x 14.5" (W) x 7.6" (H)
Printer Weight	21.3 lbs.
BOX INFORMATION	
Printer Box Dimensions ²⁸	21.7" (L) x 10.7" (W) x 19.0" (H)
Printer Box Weight	26.5 lbs.
DATE	
Availability	August 2018

PALLET INFORMATION	
Number of Printers per Layer	8
Number of Layers per Pallet	2
Total Number of Printers Per Pallet	16
Dimensions (Pallet & Printers)	48.0" (L) x 44.0" (W) x 43.8" (H)
Dimensions without Pallet	43.7" (L) x 42.0" (W) x 38.3" (H)
Loaded Pallet Weight	416.8 lbs.

DISCLAIMERS

SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE. ALL VIEWSCREEN AND OUTPUT IMAGES ARE SIMULATED.

- 1 Wireless printing and scanning requires a working network with wireless 802.11b/g/n capability, operating at 2.4GHz. Wireless performance may vary based on terrain and distance between the printer and wireless network clients.
- 2 AirPrint functionality requires a compatible iPad, iPhone, or iPod Touch device running iOS 7.0 or later, and an AirPrint-enabled printer connected to the same network as your iOS device. A printer connected to the USB port of your Mac, PC, AirPort Base station, or Time Capsule is not supported.
- 3 Requires Android mobile device with Android 4.4 operating system or later with the Mopria Print Service pre-loaded with that device and the compatible PIXMA printer on the same wireless network. The Mopria experience is also available on Android 4.4 mobile devices with a download of the Mopria Print Service from Google Play.
- 4 Compatible memory cards include SD Card and SDHC Card. The following can be used with the addition of a special adapter sold separately: miniSD Card, miniSDHC Card, microSD Card, microSDHC Card and microSDXC Card. Supported File Formats include: JPEG and TIFF (Exif-compliant) taken by DCF(Ver.1.0/2.0) compliant digital cameras. (Exif ver.2.2/2.21/2.3 compliant).
- 5 Requires a smart device with the Canon PRINT Inkjet/SELPHY app installed and connected to the desired active wireless network to complete cableless setup.
- 6 Compatible with iPad, iPhone or iPod touch devices running iOS 9.0 or later, or Android mobile devices running Android 5.1 or later, with Bluetooth hardware enabled. For full print functionality Canon PRINT Inkjet/SELPHY app must be open and paired to use Bluetooth functions, available for free on the App Store and at Google Play. Bluetooth communication and functionality cannot be guaranteed on all Android devices.
- 7 Paper types NOT supported for borderless printing are as follows: Envelope, High Resolution Paper, T-Shirt Transfer and Photo Stickers. The maximum borderless printing size is 11"x17" / 12"x12".
- 8 Requires an Internet connection and the Canon PRINT Inkjet/SELPHY app, available for free on the App Store and at Google Play. Compatible with iPad, iPhone 3GS or later, and iPod touch 3rd generation or later devices running iOS 7.0 or later, and Android mobile devices running Android 2.3.3 or later. Your device must be connected to the same working network with wireless 802.11 b/g/n/ac/ad capability as your printer. Requires a compatible social media account and is subject to that social media account's Terms of Service. Certain exceptions may apply.
- 9 The Easy-PhotoPrint Editor software requires an Internet connection and is compatible with the following operating systems; Microsoft Windows 10 (64-bit/32-bit), Microsoft Windows 8.1 (64-bit/32-bit), Microsoft Windows 7 SP1 (64-bit/32-bit), macOS High Sierra v10.13, macOS Sierra v10.12, Mac OS X El Capitan v10.11 and Mac OS X El Capitan v10.10.5. Minimum Windows and macOS/Mac OS X requirements are: 2GB of RAM and a monitor with 1024x768 resolution. The Easy-PhotoPrint Editor mobile application requires an Internet connection and the Easy-PhotoPrint Editor app v1.1.0, available for free on the App Store and at Google Play. Compatible with iPad Air 2 (2nd Generation), iPad Mini 4 and iPhone 6s or later devices running iOS 10 or later, and Android mobile devices running Android 5.x or later. Certain exceptions may apply. The following file formats are supported: JPEG, PNG, HEIF (devices running iOS 11 and mac OS v10.13 or later), DLP save data, Poster Artist export data, EasyPhoto+ export data, Easy-PhotoPrint Editor export data.
- 10 Requires an Internet connection and Google account. Subject to Google Terms of Service. Certain exceptions may apply.
- 11 Requires an Internet connection and the Message In Print app (Version 1.1), available for free on the App Store and at Google Play. Compatible with iPad and iPhone 6 or later devices running iOS 10 or later, and Android mobile devices running Android 5.1 or later. Your device must be connected to the same working network with wireless 802.11 b/g/n/ac/ad capability as your printer. Requires original content to be created using the Message In Print app/service, then printed on a compatible Canon Printer released in August 2009 or later and delivered to recipient, who views image and content through the compatible Message In Print app on their compatible device. Compatible paper sizes include 3.5"x3.5", 4" x 4" Square, 4" x 6" and 5" x 5" Square only, and compatible media types include Genuine Canon Photo Paper Glossy, Photo Paper Semi-Gloss, Photo Paper Luster and Photo Paper Matte only. Certain exceptions may apply.
- 12 Requires an Internet Connection.
- 13 DPS over IP compatible device required.
- 14 Document print speeds are the averages of ESAT in Office Category Test for the default simplex mode, ISO/IEC 24734. Photo print speed is based on the default setting using ISO/JIS-SCID N2 on Photo Paper Plus Glossy II and does not take into account data processing time on host computer. Print speed may vary depending on system configuration, interface, software, document complexity, print mode, page coverage, type of paper used etc. Copy speeds are the average of sFCOT and sESAT, ISO/IEC 29183. Copy speed may vary depending on document complexity, copy mode, page coverage, type of paper used etc. and does not take into account warming up time. See www.usa.canon.com/ipm for additional details.
- 15 Resolution may vary based on printer driver setting. Color ink droplets can be placed with a horizontal pitch of 1/4800 inch at minimum.
- 16 Auto Scan Mode is only available when scanning using a computer using the "IJ Scan Utility" or "IJ Scan Utility Lite" software.
- 17 Optical resolution is a measure of maximum hardware sampling resolution, based on ISO 14473 standard.
- 18 Based on accelerated testing by Canon in dark storage under controlled temperature, humidity and gas conditions, simulating storage in an album with plastic sleeves. Canon cannot guarantee the longevity of prints; results may vary depending on printed image, drying time, display/storage conditions, and environmental factors. See www.usa.canon.com/chromalife100 for additional details.
- 19 CREATIVE PARK PREMIUM is a premium content service available exclusively to users only when all of the colors of genuine Canon inks and all of the software that came with the printer are properly installed.
- 20 Requires an active smart assistant account linked and accompanying app enabled, the smart device and printer to be actively connected with permission to the Canon Inkjet Cloud Printing Center, and the required action(s), skill(s), or applet(s) available/enabled to the compatible printer. Voice commands can not be displayed as text on Amazon smart devices with screens.
- 21 Requires an active IFTTT account, the printer to be actively connected with permission to the Canon Inkjet Cloud Printing Center, and an IFTTT 'applet' installed/enabled and required active account/service linked to the printer.
- 22 Operation can only be guaranteed on a PC with pre-installed Windows 10, Windows 8.1, Windows 7 SP1.
- 23 Internet Connection required during software installation. For full compatibility macOS v10.12.1 or later is recommended.
- 24 Some functions may not be available with these Operating Systems. Please refer to the manual or website for details.
- 25 Requires "Canon Print Plug-in" available for free from the Amazon Appstore and an Amazon Fire Phone, Amazon Kindle Fire HD6 or HDX7 device or later running Fire OS 4.0 or later.
- 26 PosterArtist Lite software v2.60.00 is compatible with 64/32 bit versions of Microsoft Windows*10, Windows 8.1, Windows 8, Windows 7 and Windows Vista*, and only compatible with Canon PIXMA (released after July 2015), MAXIFY, imagePROGRAF and Océ printers. Minimum computer system requirements: Pentium4 2.4Ghz CPU or higher with 1GB RAM, 1024x768 pixel display and 5GB of system hard drive space.
- 27 Warranty programs are subject to certain conditions and restrictions. See www.usa.canon.com/support for details.
- 28 Product box dimensions measured in vertical box configuration.



©2018 Canon U.S.A., Inc. Canon and PIXMA are registered trademarks of Canon Inc. in the U.S. and may be registered trademarks or trademarks in other countries. Microsoft, Windows, the Windows logo and Internet Explorer are trademarks or registered trademarks of the Microsoft group of companies in the U.S. and other countries. Apple, iPad, iPhone, iPod touch and Time Capsule are registered trademarks of Apple Inc. Android, Google Assistant, and Google Play are trademarks of Google Inc. The Mopria logo is a trademark of Mopria Alliance, Inc. Amazon, Alexa, Fire, and all related logos are trademarks of Amazon.com, Inc. or its affiliates. The USB-IF logo is a trademark of Universal Serial Bus Implementers Forum, Inc. Wi-Fi is a registered trademark of the Wi-Fi Alliance. The 'Wi-Fi CERTIFIED' logo is a certification mark of the Wi-Fi Alliance. The Wi-Fi Protected Setup Mark is a mark of the Wi-Fi Alliance. All other product and brand names are trademarks of their respective owners. As an ENERGY STAR® partner, Canon U.S.A., Inc. has certified this product as meeting the ENERGY STAR® energy efficiency criteria through an EPA-recognized certification body.