



Virex® II 256

One-Step Disinfectant Cleaner and Deodorant

A one-step, quaternary disinfectant cleaner and deodorant to clean and disinfect hard surfaces.

Features & Benefits

- Kills microorganisms including HIV-1, VRE, MRSA, GRSA, MRSE, VISA, PRSP, Herpes Simplex Types 1&2, Influenza Type A2, Adenovirus, Rotavirus and many more
- Kills the organisms that cause odors and works as an odor counteractant to further eliminate odors not associated with bacteria
- Highly concentrated quaternary formula provides excellent one-step, cost-effective cleaning and disinfection

Applications

- Used in medical and general institutional facilities
- Use solution is neutral to floor finish so it will not dull, pit or soften floor finishes





Virex® II 256

One-Step Disinfectant Cleaner and Deodorant

Use instructions

- Add the product at ½ oz. per gallon of water (1:256).
- Pre-clean heavily soiled areas.

For Use as a One-Step Cleaner/Disinfectant

- Apply use solution to hard, non-porous environmental surfaces. To disinfect, all surfaces must remain wet for 10 minutes.
- Air Dry, wipe surfaces to dry and remove any residue, or rinse with potable water as necessary.

Note: Rinsing is not necessary unless floors are to be coated with finish or restorer. All food contact surfaces such as appliances and kitchen countertops must be rinsed with potable water. Do not use on glassware, utensils or dishes.

For Use as a Cleaner and Deodorizer

- Apply use solution to hard, non-porous surfaces. Air Dry, wipe surfaces to dry and remove any residue, or rinse with potable water as necessary.

For Use as a Non-Acid Bowl Cleaner/Disinfectant in Toilet Bowls and Urinals from Use-Dilution

- Empty toilet bowls by forcing water through the trap. Apply use solution to exposed surfaces in toilet bowls and urinals. Swab entire surface area especially under rim. Allow entire surface to remain wet for 10 minutes. Flush toilet or urinal and rinse swab applicator thoroughly.

For Use to Clean and Disinfect Shower Rooms, Locker Rooms and Other Large, Open Areas with Floor Drains

- Apply use solution to floors, walls and ceilings. All surfaces must remain wet for 10 minutes. Scrub and rinse surfaces thoroughly and let air dry.

To Kill Mold, Mildew and Fungi (in 5% soil load)

- Apply use solution to hard, non-porous environmental surfaces and allow surfaces to remain wet for 10 minutes. Wipe and let air dry.

To Control Mold and Mildew

- Apply use solution to pre-cleaned hard, non-porous environmental surfaces and allow to air dry. Repeat weekly or when growth reappears.

SmartDose™ Icons



Spray
Bottle
1:256



Mop Bucket
(2 pumps)
1:256

Technical data	Virex® II 256
EPA Reg. No.	70627-24
Color/Form	Transparent blue liquid
pH	10.2 (Concentrate) / 8.8 (Use Dilution)
Scent	Minty
Shelf Life	36 months (Concentrate) / 1 year (Use Dilution)

Product	Pack size	Dilution	Product code	
Virex® II 256	2 x 1.5 L / 1.58 U.S. Qt. RTD® Units	1:256	3062637	
Virex® II 256	1 x 5 L / 1.32 U.S. Gal. RTD® Unit	1:256	3062768	
Virex® II 256	2 x 2.5 L / 84.5 oz. J-Fill® Bottles	1:256	04329.	
Virex® II 256	6 x 946 mL / 32 fl. oz. AccuMix® Containers	1:256	04331.	
Virex® II 256	4 x 3.78 L / 1 U.S. Gal. Containers	1:256	04332.	
Virex® II 256	2 x 1.4 L / 1.48 U.S. Qt. SmartDose™ Bottles	1:256 (Spray Bottle), 1:256 (Mop Bucket)	5019317	
Virex® II 256	2 x 5.68 L / 1.5 U.S. Gal. Command Center® Units	1:256	5271416	
Virex® II 256	12 x 946 mL / 32 fl. oz. Spray Bottles		D03916	

Safe handling

Please make sure your employees read and understand the product label and Safety Data Sheet before using this product. The label contains directions for use; and both the label and SDS contain hazard warnings, precautionary statements and first aid procedures. SDS are available online at www.diversey.com or by calling 888.352.2249. Improper use or dilution may result in damage to surfaces and may result in health and physical hazards that match those of the concentrate. Please refer to the Diversey HazMat Library, only available through Internet Explorer, <http://naextranet.diversey.com/dot/>, for up-to-date shipping information.